

Scout RX3 Home Vision
Robot vacuum cleaner
with live image feed and 170 minutes' runtime.



- Top-class dust pickup thanks to Quattro Cleaning Power
- Systematic cleaning with 3D Smart Navigation
- Convenient operation with the Miele Scout app
- Check that everything's OK at home with Home Vision HD
- Particularly long battery charge* – #170 minutes non-stop#Z
- Protects furniture with Furniture Protection Technology

* measured in the Silent cleaning mode, in a standard environment according to IEC 62929:2014

EAN: 4002516453895 / Material number: 11830100 / Old Material Number: 41PQL030USA

Construction type	
Robot vacuum cleaner	•
Product line	Scout RX3
Product type	SPQL0
Appliance color	Rose gold (PF)
Cleaning	
Cleaning system	Quattro Cleaning Power
Navigation	
Navigation	3D Smart Navigation
Advanced Corner Cleaning	•
Non-Stop Power	•
Furniture Protection Technology	•
Cleaning area in m ²	140
Operating time in min.	170
Recharging time in min.	240
Max. carpet height in in. (mm)	0 3/4 (17)
Control panel	
Cleaning programs	4
Auto-Mode	•
Spot-Mode	•
Turbo-Mode	•
Silent mode	•
Manual cleaning	•
Timer	Every day is different
Touch User Interface	•
App	
MobileControl	•
Home Mapping	•
Home Vision	•
Mobility	
Flat design in in.(mm)	3 3/8 (85)
Filter system	
Exhaust filter	AirClean Plus filter
Dust bin volume in cu. ft. (l)	0.4
Technical data	
Battery type	Li-Ion
Nominal battery capacity in mAh	5200
Volume in dB	71.0
Width in inches (mm)	14 (354)
Height in inch (mm)	85
Weight in lbs (kg)	8 (3.2)
Accessories supplied	
Filter	AirClean Plus filter
Remote control	•
Base station	•
Adapter	•
Cleaning brush	integrated
Area demarcation	magnetic tape
Replacement filters	1 Filter