

M 7240 TC AM

Built-in microwave oven, 24" width
in a design that is the perfect complement with controls on the top.



- Clear text display with sensor controls – DirectSensor S
- Perfect defrosting and cooking – Automatic Programs
- Plenty of space – 1.62 cu. ft. oven capacity & 15 3/4" turntable
- Very powerful microwave – 900 W
- What you want at the touch of a button – Popcorn button

EAN: 4002516540618 / Material number: 11845600 / Old Material Number: 24724040USA

Design	
Appliance color	Clean Touch Steel
Construction type and design	
Built-in microwave oven	•
PureLine	•
TopControl	•
Convenience features	
Keep-warm function	•
Operating modes	
MasterChef automatic programs	•
Microwave solo operation	•
User convenience	
Display	DirectSensor S
SoftOpen	•
SoftClose	•
Multilingual	•
Popcorn function	•
Time of day display	•
Minute minder	•
Programmable cooking time	•
Minute Plus button	•
Individual settings	•
Efficiency and sustainability	
Night dimming	•
Cleaning convenience	
Clean Touch Steel surface	•
Stainless-steel oven cavity	•
CleanGlass door	•
Safety	
Appliance cooling system and cool touch front	•
System lock	•
Safety switch	•
Child lock "Door" in display	•
Technical data	
Cavity volume in cu.ft (l)	1.62 (46)
Door hinge side	Bottom
Oven interior lighting	1 LED spot
Cavity height in in. (cm)	9 1/4 (23.2)
Turntable diameter in in. (cm)	16 (40.6)
Electronically controlled microwave power	•
Microwave power levels	1-7
Maximum microwave output in W	900
Niche width min. in inches (mm)	22 1/4 (562)
Niche width max. in inches (mm)	22 3/8 (568)
Niche height min. in inches (mm)	17 3/4 (450)
Niche height max. in inches (mm)	17 7/8 (452)
Niche depth in in. (mm)	550
Appliance dimensions (W x H x D) in inches (mm)	23 1/2 (595) x 18 (456) x 22 1/8 (560)
Appliance width in in. (mm)	23 1/2 (595)

M 7240 TC AM

Built-in microwave oven, 24" width

in a design that is the perfect complement with controls on the top.



EAN: 4002516540618 / Material number: 11845600 / Old Material Number: 24724040USA

Appliance height in in. (mm)	18 (456)
Appliance depth in in. (mm)	22 1/8 (560)
Niche-independent venting	•
Weight in lbs. (kg)	63 (28.3)
Total connected load in kW	1.6
Power Rating in V	120
Frequency in Hz	60
Fuse rating in A	10
Number of phases	1
Connection wire with plug	•
Length of power cord in in. (m)	2.10

Standard accessories


Available display languages

Available display languages via MultiLingua


bahasa malaysia, dansk, deutsch, english, español, français, hrvatski, italiano, magyar, nederlands, norsk, polski, português, русский, română, slovenčina, slovenščina, srpski, suomi, svenska, türkçe, українська, čeština, ελληνικά,

M 7240 TC AM


Built-in microwave oven, 24" width
in a design that is the perfect complement with controls on the top.




M7240TC(+EBA7848), side view, 30 Zoll, Flush Inset
7/8" – 22" mm – Glass, 15/16" – 23.3" mm – Stainless steel




M7240TC(+EBA7848), side view, 30 Zoll, Flush Inset, built-under
7/8" – 22" mm – Glass, 15/16" – 23.3" mm – Stainless steel




M7240TC Einbau, 30 Zoll, Flush inset
7/8" – 22" mm – Glass, 15/16" – 23.3" mm – Stainless steel




M7240TC+EBA7848, Einbau, 30 Zoll, Flush inset
7/8" – 22" mm – Glass, 15/16" – 23.3" mm – Stainless steel




M7x4xTC, Einbau, 30 Zoll, Flush inset, wide front
7/8" – 22" mm – Glass, 15/16" – 23.3" mm – Stainless steel




M7240TC+EBA7848, Einbau, 30 Zoll, Flush inset, wide front
7/8" – 22" mm – Glass, 15/16" – 23.3" mm – Stainless steel



M7240TC, Einbau, 30 Zoll, Flush inset, built-under
7/8" – 22" mm – Glass, 15/16" – 23.3" mm – Stainless steel




M7240TC+EBA7848, Einbau, 30 Zoll, Flush inset, built-under
7/8" – 22" mm – Glass, 15/16" – 23.3" mm – Stainless steel



M7240TC, Einbau, 30 Zoll, Flush Inset, built-under, wide front
7/8" – 22" mm – Glass, 15/16" – 23.3" mm – Stainless steel


M 7240 TC AM

Built-in microwave oven, 24" width
in a design that is the perfect complement with controls on the top.




M7240TC+EBA7848, Einbau, 30 Zoll, Flush inset, built-under, wide front

7/8" – 22" mm – Glass, 15/16" – 23.3" mm – Stainless steel




M7240(+EBA7848), Installation, 30 Zoll, Flush inset

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation. – Electrical and water supplies are recommended to be placed in adjacent cabinetry. Additional cabinet depth is required when placing the electrical and water supplies behind the appliance. E = Electric connection




M7240(+EBA7848), Installation, 30 Zoll, Flush inset, built-under

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation. – Electrical and water supplies are recommended to be placed in adjacent cabinetry. Additional cabinet depth is required when placing the electrical and water supplies behind the appliance. E = Electric connection




M7240(+EBA7848), Installation, 30 Zoll, Flush inset, wide front

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation. – Electrical and water supplies are recommended to be placed in adjacent cabinetry. Additional cabinet depth is required when placing the electrical and water supplies behind the appliance. E = Electric connection



M7240(+EBA7848), Installation, 30 Zoll, Flush inset, wide front

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation. – Electrical and water supplies are recommended to be placed in adjacent cabinetry. Additional cabinet depth is required when placing the electrical and water supplies behind the appliance. E = Electric connection




M7240TC, M7240TC+EBA7848, 30 Zoll, Proud

7/8" – 22" mm – Glass, 15/16" – 23.3" mm – Stainless steel


M 7240 TC AM

Built-in microwave oven, 24" width
in a design that is the perfect complement with controls on the top.




M7240TC, M7240TC+EBA7848, 30 Zoll, Proud, built-under


7/8" – 22" mm – Glass, 15/16" – 23.3" mm – Stainless steel




M7240TC, Einbau, 30 Zoll, Proud




M7240TC+EBA7848, Einbau, 30 Zoll, Proud




M7240TC, Einbau, 30 Zoll, Proud, wide front




M7240TC+EBA7848, Einbau, 30 Zoll, Proud, wide front




M7240TC, Einbau, 30 Zoll, Proud, built-under



M7240TC+EBA7848, Einbau, 30 Zoll, Proud, built-under




M7240TC, Einbau, 30 Zoll, Proud, built-under, wide front



M7240TC+EBA7848, Einbau, 30 Zoll, Proud, built-under, wide front


M 7240 TC AM

Built-in microwave oven, 24" width
in a design that is the perfect complement with controls on the top.




M7240TC(+EBA7848), Installation, 30 Zoll, Proud

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation. – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection




M7x4xTC(+EBA7848), Installation, 30 Zoll, Proud, built-under

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation. – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection




M7240TC(+EBA7848), Installation, 30 Zoll, Proud, wide front

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation. – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection




M7240TC(+EBA7848), Installation, 30 Zoll, Proud, built-under, wide front

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation. – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection



M7240TC(+EBA7848), Seitenansicht, 30 Zoll, Proud, Oberschrank – Skizze – NA


7/8" – 22* mm – Glass, 15/16" – 23.3** mm – Stainless steel




M7240TC, Einbau, 30 Zoll, Proud, Oberschrank – Skizze – NA

M 7240 TC AM


Built-in microwave oven, 24" width
in a design that is the perfect complement with controls on the top.




M7240TC(+EBA7848), Einbau, 30 Zoll, Proud, Oberschrank – Skizze – NA



M7240TC, Einbau, 30 Zoll, Proud, breite Front, Oberschrank – Skizze – NA




M7240TC(+EBA7848), Einbau, 30 Zoll, Proud, breite Front, Oberschrank – Skizze – NA




M7240TC(+EBA7848), Einbau, 30 Zoll, Proud, Oberschrank – Skizze – NA

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, ! – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., , E = Electric connection




M7240TC(+EBA7848), Einbau, 30 Zoll, Proud, breite Front, Oberschrank – Skizze – NA

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, ! – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., , E = Electric connection




M7240SC(+EBA7848), Seitenansicht, 30 Zoll, Flush, inset, Oberschrank – Skizze – NA


7/8" – 22" mm – Glass, 15/16" – 23.3" mm – Stainless steel



M7240TC, Einbau, 30 Zoll, Flush, inset, Oberschrank – Skizze – NA




M7240SC(+EBA7848), Einbau, 30 Zoll, Flush, inset, Oberschrank – Skizze – NA




M7240TC, Einbau, 30 Zoll, Flush, inset, breite Front, Oberschrank – Skizze – NA

M 7240 TC AM

Built-in microwave oven, 24" width
in a design that is the perfect complement with controls on the top.




M7240SC(+EBA7848), Einbau, 30 Zoll, Flush, inset, breite Front, Oberschrank – Skizze – NA



M7240SC(+EBA7848), Installation, 30 Zoll, Flush, inset, Oberschrank – Skizze – NA

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, ! – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection



M7240SC(+EBA7848), Installation, 30 Zoll, Flush, inset, breite Front, Oberschrank – Skizze – NA

A – Cut-out (4" x 28" / 100 mm x 720 mm) in the bottom of the cabinet for power cord and ventilation, ! – Electrical and water supplies are recommended to be placed in adjacent cabinetry., Additional cabinet depth is required when placing the electrical and water supplies behind the appliance., E = Electric connection