

KMR 1136-3LP GD EDST/CLST RangeTop

with ?? burners and griddle for versatility and performance



- Professional design – 36 (914) in (mm) wide in stainless steel with Clean Touch Steel™ finishing
- Direct control – metal knobs with light ring
- Easy cleaning – ComfortClean dishwasher-safe grates
- Broad performance spectrum – burner w. up to 19,500 BTU (5.7 kW)
- Convenient and safe – automatic re-ignition for all burners

EAN: 4002516495444 / Material number: 11852550 / Old Material Number: 26113671USA

Heating type	
Fuel type	Gas
Design	
Rangetop	•
Design	
Casing	Stainless steel
Front panel	CleanSteel
Genuine metal knobs	•
Cast iron pot rests (matte black enameled)	•
Cooking zone details	
Number of gas burners	4
Number of griddle surfaces	1
1st cooking zone/cooking area	
Position	front left
Type	Ultra high-speed burner
Minimum power output in BTU/hr	1500
Maximum power output in BTU/hr	19500
Max. rating in W	5700
2nd cooking zone/cooking area	
Position	rear left
Type	High-speed burner
Minimum power output in BTU/hr	1500
Maximum power output in BTU/hr	12500
Max. rating in W	2300
3rd cooking zone/cooking area	
Position	Centered
Type	Griddle surface
Maximum power output in BTU/hr	14300
Max. rating in W	4200
4th cooking zone/cooking area	
Position	rear right
Type	High-speed burner
Minimum power output in BTU/hr	1500
Maximum power output in BTU/hr	19500
Max. rating in W	2600
5th cooking zone/cooking area	
Position	front right
Type	Ultra high-speed burner
Minimum power output in BTU/hr	1500
Maximum power output in BTU/hr	19500
Max. rating in W	5700
8th cooking zone/cooking area	
True Simmer function	•
Width of griddle surface in in.(mm)	10 1/4 (258)
Depth of griddle surface in in.(mm)	17 1/8 (434)
User convenience	
Operation via genuine metal knobs with backlit	•
Cleaning convenience	
Dishwasher-safe trivets	•
Single-piece cooktop surround	•

KMR 1136-3LP GD EDST/CLST

RangeTop

with ?? burners and griddle for versatility and performance



EAN: 4002516495444 / Material number: 11852550 / Old Material Number: 26113671USA

Safety

Automatic re-ignition

•

Technical data

Dimensions (width) in in. (mm)

36 (914)

Dimensions (height) in in. (mm)

7 5/8 (191)

Dimensions (depth) in in. (mm) with bullnose

27 1/4 (692)

Dimensions (depth) in in. (mm) without bullnose

25 5/8 (650)

Weight in lbs. (kg)

152 (69)

Total output in BTU/hr

85300

Total connected load in kW

24.60

Voltage in V

120

Fuse rating in A

10

Number of phases

1

Power cord length in in. (m)

3 (1.2)