

## KMR 1354-3 G EDST/CLST 48-inch RangeTop



- Professional design – 48 (1219) in (mm) wide in stainless steel with Clean Touch Steel™ finishing
- Direct control – metal knobs with light ring
- Easy cleaning – ComfortClean dishwasher-safe grates
- Broad performance spectrum – burner w. up to 19,500 BTU (5.7 kW)
- Convenient and safe – automatic re-ignition for all burners

EAN: 4002516537113 / Material number: 11852560 /  
Old Material Number: 26135470USA

|  |                         |
|--|-------------------------|
| <b>Heating type</b>                        |                         |
| Fuel type                                  | Gas                     |
| <b>Design</b>                              |                         |
| RangeTop                                   | •                       |
| <b>Design</b>                              |                         |
| Casing                                     | Stainless steel         |
| Front panel                                | CleanSteel              |
| Genuine metal knobs                        | •                       |
| Cast iron pot rests (matte black enameled) | •                       |
| <b>Cooking zone details</b>                |                         |
| Number of gas burners                      | 8                       |
| <b>1st cooking zone/cooking area</b>       |                         |
| Position                                   | front left              |
| Type                                       | Ultra high-speed burner |
| Minimum power output in BTU/hr             | 1700                    |
| Maximum power output in BTU/hr             | 19500                   |
| Max. rating in W                           | 5700                    |
| <b>2nd cooking zone/cooking area</b>       |                         |
| Position                                   | rear left               |
| Type                                       | High-speed burner       |
| Minimum power output in BTU/hr             | 1200                    |
| Maximum power output in BTU/hr             | 12500                   |
| Max. rating in W                           | 2900                    |
| <b>3rd cooking zone/cooking area</b>       |                         |
| Position                                   | Rear center left        |
| Type                                       | Ultra high-speed burner |
| Minimum power output in BTU/hr             | 1700                    |
| Maximum power output in BTU/hr             | 19500                   |
| Max. rating in W                           | 4000                    |
| <b>4th cooking zone/cooking area</b>       |                         |
| Position                                   | Rear center right       |
| Type                                       | Ultra high-speed burner |
| Minimum power output in BTU/hr             | 1700                    |
| Maximum power output in BTU/hr             | 19500                   |
| Max. rating in W                           | 4000                    |
| <b>5th cooking zone/cooking area</b>       |                         |
| Position                                   | rear right              |
| Type                                       | High-speed burner       |
| Minimum power output in BTU/hr             | 1200                    |
| Maximum power output in BTU/hr             | 12500                   |
| Max. rating in W                           | 2900                    |
| <b>6th cooking zone/cooking area</b>       |                         |
| Position                                   | front right             |
| Type                                       | Ultra high-speed burner |
| Minimum power output in BTU/hr             | 1700                    |
| Maximum power output in BTU/hr             | 19500                   |
| Max. rating in W                           | 5700                    |


## KMR 1354-3 G EDST/CLST 48-inch RangeTop



EAN: 4002516537113 / Material number: 11852560 /  
Old Material Number: 26135470USA

| <b>7th cooking zone/cooking area</b>            |                         |
|---|-------------------------|
| Position  | Center right front      |
| Type  | Ultra high-speed burner |
| Minimum power output in BTU/hr                  | 1700                    |
| Maximum power output in BTU/hr                  | 19500                   |
| Max. rating in W                                | 5700                    |
| <b>8th cooking zone/cooking area</b>            |                         |
| Position  | Center left front       |
| Type  | Ultra high-speed burner |
| Minimum power output in BTU/hr                  | 1700                    |
| Maximum power output in BTU/hr                  | 19500                   |
| Max. rating in W                                | 5700                    |
| True Simmer function                            | •                       |
| <b>User convenience</b>                         |                         |
| Operation via genuine metal knobs with backlit  | •                       |
| <b>Cleaning convenience</b>                     |                         |
| Dishwasher-safe trivets                         | •                       |
| Single-piece cooktop surround                   | •                       |
| <b>Safety</b>                                   |                         |
| Automatic re-ignition                           | •                       |
| <b>Technical data</b>                           |                         |
| Dimensions (width) in in. (mm)                  | 48 (1219)               |
| Dimensions (height) in in. (mm)                 | 7 5/8 (191)             |
| Dimensions (depth) in in. (mm) with bullnose    | 27 1/4 (692)            |
| Dimensions (depth) in in. (mm) without bullnose | 25 5/8 (650)            |
| Weight in lbs. (kg)                             | 149 (68)                |
| Total output in BTU/hr                          | 142000                  |
| Total connected load in kW                      | 41.60                   |
| Voltage in V                                    | 120                     |
| Fuse rating in A                                | 10                      |
| Number of phases                                | 1                       |
| Power cord length in in. (m)                    | 3 (1.2)                 |

## KMR 1354-3 G EDST/CLST 48-inch RangeTop



KMR1354 G/LP, KMR1355 G/LP, KMR1356 G/LP,  
KMR1354-3, KMR1355-3, KMR1356-3 (installation  
drawings)

1) Side view, 2) Front view, 3) Rear view, 4) Gas  
connection, 5) Electrical connection,