

## KMR 1355-3 G GR EDST/CLST 48-inch RangeTop



- Professional design – 48 (1219) in (mm) wide in stainless steel with Clean Touch Steel™ finishing
- Direct control – metal knobs with light ring
- Easy cleaning – ComfortClean dishwasher-safe grates
- Broad performance spectrum – burner w. up to 19,500 BTU (5.7 kW)
- Convenient and safe – automatic re-ignition for all burners

EAN: 4002516495451 / Material number: 11852600 /  
Old Material Number: 26135570USA

<b>Heating type</b>	
Fuel type	Gas
<b>Design</b>	
RangeTop	•
<b>Design</b>	
Casing	Stainless steel
Front panel	CleanSteel
Genuine metal knobs	•
Cast iron pot rests (matte black enameled)	•
<b>Cooking zone details</b>	
Number of gas burners	6
Number of grill surfaces	1
<b>1st cooking zone/cooking area</b>	
Position	front left
Type	Ultra high-speed burner
Minimum power output in BTU/hr	1700
Maximum power output in BTU/hr	19500
Max. rating in W	5700
<b>2nd cooking zone/cooking area</b>	
Position	rear left
Type	High-speed burner
Minimum power output in BTU/hr	1200
Maximum power output in BTU/hr	12500
Max. rating in W	3700
<b>3rd cooking zone/cooking area</b>	
Position	left center
Type	Grill surface
Minimum power output in BTU/hr	13000
Maximum power output in BTU/hr	19000
Max. rating in W	5500
<b>4th cooking zone/cooking area</b>	
Position	Rear center right
Type	Ultra high-speed burner
Minimum power output in BTU/hr	1700
Maximum power output in BTU/hr	19500
Max. rating in W	5700
<b>5th cooking zone/cooking area</b>	
Position	rear right
Type	High-speed burner
Minimum power output in BTU/hr	1200
Maximum power output in BTU/hr	12500
Max. rating in W	3700
<b>6th cooking zone/cooking area</b>	
Position	front right
Type	Ultra high-speed burner
Minimum power output in BTU/hr	1700
Maximum power output in BTU/hr	19500
Max. rating in W	5700


## KMR 1355-3 G GR EDST/CLST 48-inch RangeTop



EAN: 4002516495451 / Material number: 11852600 /  
Old Material Number: 26135570USA

<b>7th cooking zone/cooking area</b>	
Position	Center right front
Type	Ultra high-speed burner
Minimum power output in BTU/hr	1700
Maximum power output in BTU/hr	19500
Max. rating in W	5700
<b>8th cooking zone/cooking area</b>	
True Simmer function	•
Width of broil surface in in.(mm)	11 1/4 (284)
Depth of broil surface in in.(mm)	22 1/8 (560)
<b>User convenience</b>	
Operation via genuine metal knobs with backlit	•
<b>Cleaning convenience</b>	
Dishwasher-safe trivets	•
Single-piece cooktop surround	•
<b>Safety</b>	
Automatic re-ignition	•
<b>Technical data</b>	
Dimensions (width) in in. (mm)	48 (1219)
Dimensions (height) in in. (mm)	7 5/8 (191)
Dimensions (depth) in in. (mm) with bullnose	27 1/4 (692)
Dimensions (depth) in in. (mm) without bullnose	25 5/8 (650)
Weight in lbs. (kg)	160 (73)
Total output in BTU/hr	122000
Total connected load in kW	35.70
Voltage in V	120
Fuse rating in A	10
Number of phases	1
Power cord length in in. (m)	3 (1.2)

## KMR 1355-3 G GR EDST/CLST 48-inch RangeTop



KMR1354 G/LP, KMR1355 G/LP, KMR1356 G/LP,  
KMR1354-3, KMR1355-3, KMR1356-3 (installation  
drawings)

1) Side view, 2) Front view, 3) Rear view, 4) Gas  
connection, 5) Electrical connection,