

CM 5510 Silence  
Countertop coffee machine  
with OneTouch for Two for the ultimate in coffee enjoyment.



- 2 coffees at once at the touch of a button – OneTouch for Two
- Perfect results and intense coffee flavor – AromaticSystem
- Creamy milk froth for a wide range of specialty coffees
- Convenient cleaning programs for care and maintenance
- Convenient when hosting lots of guests – coffee/tea pot function

EAN: 4002516462781 / Material number: 11861030 / Old Material Number: 29551008USA

Construction type and design	
Countertop bean-to-cup coffee machine	•
Color	AluSilver Metallic
Convenience features	
AromaticSystem	•
OneTouch preparation	•
One Touch and OneTouch for Two	•
Programmable User profile	2
Flavor preserving conical grinding unit	•
Grinding grade selectable	•
Additional coffee types in ground coffee form possible	•
Ground quantity programmable	•
Water quantity programmable	•
Water temperature programmable	•
Amount of milk can be programmed	•
Amount of milk froth can be programmed	•
Pre-brewing programmable	•
User convenience	
Control panel	DirectSensor
Height adjustment of infinitely adjustable central spout min in in.(cm)	3 1/4 (8.0)
Height adjustment of infinitely adjustable central spout max in in.(cm)	5 3/8 (13.5)
Multilingua	•
No. of bean types	1
No. of bean containers	1
Bean container capacity, each in oz (g)	200
Bean container capacity, total in oz (g)	7.05 (200)
Capacity of water container in fl oz (l)	43.96 (1.3)
Capacity of waste container in servings	7
Drip tray capacity in fl oz (l)	27.05 (0.8)
Easily accessible containers	•
Programmable stand-by time	•
Individual settings	•
Drink specialties	
Adjustable beverage portion size in ml	20-300
Ristretto, single	•
Ristretto, double	•
Espresso, single	•
Espresso, double	•
Coffee, single	•
Coffee, double	•
Long coffee, single	•
Long coffee, double	•
Cappuccino, single	•
Cappuccino, double	•
Latte macchiato, single	•
Latte macchiato, double	•
Hot milk, single	•
Latte macchiato, double	•

CM 5510 Silence  
Countertop coffee machine  
with OneTouch for Two for the ultimate in coffee enjoyment.



EAN: 4002516462781 / Material number: 11861030 / Old Material Number: 29551008USA

Milk froth, single	•
Milk froth, double	•
Caffè latte, single	•
Caffè latte, double	•
Hot water, single	•
Coffee pot	•
<b>Efficiency and sustainability</b>	
Energy-saving Eco mode option	•
<b>Cleaning convenience</b>	
Manual descaling	•
Automatic rinsing of the milk pipework from the water container	•
Convenient cleaning programs	•
Auto-Off function	•
ComfortClean	•
Removable milk pipework	•
Removable brew unit	•
Adjustable water hardness	•
<b>Safety</b>	
System lock	•
<b>Technical data</b>	
Appliance width in in.(mm)	9 1/2 (241)
Appliance height in in.(mm)	14 1/4 (360)
Appliance depth in in.(mm)	18 1/8 (460)
Total connected load in kW	1.45
Voltage in V	120
Fuse rating in A	15
Number of phases	1
Length of electrical wire in ft (m)	3 (1.2)
<b>Standard accessories</b>	
Descaling tablets	•
Cleaning tablets	•
Brief operating instructions on rear of unit	•
<b>Available display languages</b>	
Available display languages via MultiLingua	bahasa malaysia, dansk, deutsch, english, español, français, hrvatski, italiano, magyar, nederland, norsk, polski, portugûes, русский, română, slovenčina, slovenščina, srpski, suomi, svenska, türkçe, українська, čeština, ελληνικά,