

DAS 4930  
Built-in ventilation hood  
with intuitive SmartControl controls



- Elegant design – Obsidian Black control panel, 90 cm wide
- Unique user convenience – Con@ctivity
- LED strip for uniform lighting
- Efficient filtration- 10-ply stainless steel grease filters
- Recirculation mode – Active AirClean or Longlife AirClean filter

EAN: 4002516496199 / Material number: 11878550 /  
Old Material Number: 28S4930BUSA

<b>Construction type and design</b>	
Color	Obsidian black
<b>Design</b>	
Built-in ventilation hood	•
<b>Operating modes</b>	
Recirculated mode	Can be retrofitted
Recirculation conversion kit (order separately)	DUU 151,DUU 150
OdorFree charcoal filter (order separately)	DKFS 31-P, DKFS 31-R
<b>User convenience</b>	
Miele@home	•
Automatic function	Con@ctivity 3.0
Electronic controls	•
SmartControl	•
Booster levels	1
Programmable Intensive switch-off	•
Delayed shutdown for 5 or 15 minutes	•
Grease filter saturation indicator	•
Active charcoal filter saturation indicator	•
<b>Cleaning convenience</b>	
Easy-to-clean CleanCover hood liner	•
<b>Filter system</b>	
Number of dishwasher-safe stainless-steel grease filters	1
<b>Lighting</b>	
LED	•
Number x W	1 x 3 W
Light intensity in lx	300 lx
Color temperature in K	3500 Kelvin
Light dimmer function	•
<b>Blower</b>	
Dual-action blower	•
AC motor	•
<b>Exhaust air</b>	
Maximum air throughput in cfm according to HVI	427
<b>Safety</b>	
Safety shut-off	•
Single-ply safety glass (ESG)	•
<b>Technical data</b>	
Canopy width in in.(mm)	35 3/8 (896)
Canopy height in in.(mm)	11/2 (36)
Canopy depth in in.(mm)	10 3/4 (273)
Net weight in lbs. (kg)	36 (16.0)
Length of electrical wire in ft (m)	2 (0.8)
Standard plug fitted	•
Minimum distance above electric cooktops in in. (mm)	24 1/8 (610)
Minimum height above gas cooktop (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	26 (660)
Number of phases	1
Total connected load in kW	0.35

DAS 4930  
Built-in ventilation hood  
with intuitive SmartControl controls



EAN: 4002516496199 / Material number: 11878550 /  
Old Material Number: 28S4930BUSA

Voltage in V	120
Fuse rating in A	15
Frequency in Hz	60

**Installation note**

Vent connection at top


•

**Standard accessories**

Non-return flap


•

## DAS 4930 Built-in ventilation hood with intuitive SmartControl controls



DAS4930, DAS4931, Installation drawings

1) The front section of the wall unit must be fitted with a base panel to secure the cooker hood. If the appliance is fitted further back, e.g. to accommodate a front panel, then the shelf depth should be deeper accordingly. 2) If a partition wall is to be provided in the unit, it must be removable. 3) Extraction, recirculation with conversion kit DUU 150. 4) Installation is also possible in a 600 mm wide unit. \* In this installation situation, the deflector plate is flush with the front edge of the housing unit carcass. . If you wish to position the cooker hood further forward or further back, dimensions have to be adapted accordingly. , Extraction: the height of the wall unit and the cut-out dimensions must take into account any accessories fitted, e.g. silencer, recirculation hood conversion kit).



DAS4930, DAS4931, drawing – US

1) Exhaust air, mounted accessories must be taken into account for dimensions of cabinet height and cutouts. 2) Exhaust air, recirculation with DUU 150 conversion kit. 3) Installation is also possible in a 600 mm wide cabinet. , \*In this installation situation, the screen is flush with the front edge of the cabinet. If the cooker hood is positioned further to the front or rear, the dimensions must be adjusted accordingly.