

DAS 8930

Built-in ventilation hood

with intuitive SmartControl White controls for use in narrow upper cabinets



- Intricate design – flat stainless-steel panel, 36 in (90 cm) wide
- Unique user convenience – Con@ctivity
- LED strip for uniform lighting
- Efficient filtration- 10-ply stainless steel grease filters
- Recirculation mode – Active AirClean or Longlife AirClean filter

EAN: 4002516495628 / Material number: 11878590 /
Old Material Number: 28S8930SUSA

Construction type and design	
Color	Stainless steel
Design	
Built-in ventilation hood	•
Operating modes	
Recirculated mode	Can be retrofitted
Recirculation conversion kit (order separately)	DUU 151
OdorFree charcoal filter (order separately)	DKF 31-P, DKF 31-R
User convenience	
Miele@home	•
Automatic function	Con@ctivity 3.0
Electronic controls	•
SmartControl	•
Booster levels	1
Programmable Intensive switch-off	•
Delayed shutdown for 5 or 15 minutes	•
Grease filter saturation indicator	•
Active charcoal filter saturation indicator	•
Cleaning convenience	
Easy-to-clean CleanCover hood liner	•
Filter system	
Number of dishwasher-safe stainless-steel grease filters	2
Lighting	
LED	•
Number x W	1 x 3 W
Light intensity in lx	270 lx
Color temperature in K	3500 Kelvin
Light dimmer function	•
Blower	
Dual-action blower	•
AC motor	•
Exhaust air	
Maximum air throughput in cfm according to HVI	418
Safety	
Safety shut-off	•
Technical data	
Canopy width in in.(mm)	34 (861)
Canopy height in in.(mm)	2 3/8 (60)
Canopy depth in in.(mm)	12 1/8 (307)
Net weight in lbs. (kg)	42 (19.0)
Length of electrical wire in ft (m)	2 (0.8)
Standard plug fitted	•
Minimum distance above electric cooktops in in. (mm)	24 1/8 (610)
Minimum height above gas cooktop (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	26 (660)
Number of phases	1
Total connected load in kW	0.35
Voltage in V	120

DAS 8930

Built-in ventilation hood

with intuitive SmartControl White controls for use in narrow upper cabinets



EAN: 4002516495628 / Material number: 11878590 /
Old Material Number: 28S8930SUSA

Fuse rating in A	15
Frequency in Hz	60

Installation note

Vent connection at top •

Vent connection at top and rear •

Installation template •



Standard accessories

Non-return flap •

DAS 8930



Built-in ventilation hood

with intuitive SmartControl White controls for use in narrow upper cabinets



DAS8930, Installation drawings

1) Extraction, recirculation with conversion kit DUU 150.,
 2) Alternative ducting connection to the rear., 3)
 Accessory DSM module., 4) The wall unit can be fitted
 with a partition after installation. The slots for the grease
 filters and, in recirculation mode, for the odor filters
 must remain accessible., The height of the wall unit
 and the cut-out dimensions must take into account
 any accessories fitted (e.g. silencer, recirculation hood
 conversion kit, DSM module)



DAS8930, drawing – US

1) Exhaust air, recirculation with DUU 150 conversion
 kit., 2) Exhaust air connection alternatively to the rear., 3)
 DSM module accessory., 4) The wall unit can be fitted
 with a partition after installation. The slots for the grease
 filters and, in the case of recirculation mode, for the odor
 filters must remain accessible. , Mounted accessories
 must be taken into account for the cabinet height and cut-
 out dimensions (e.g. silencer, recirculation air conversion
 kit, DSM module).