

APWM 017

Dispenser pump rack

with slanted base for the complete residual emptying of liquid media containers.

EAN: 4002516501404 / Material number: 11933700 / Old Material Number: 59510017EU



- Suitable for the installation of the dispenser pump casing DOS G2
- Suitable for the installation of the dispenser pump unit DOS GP3
- With four swivel castors for maximum mobility
- Suitable for installing Brightwell dispenser pumps and APWM 054

Product category	
Washing machines	•
Machine/accessory category	
PW 413	•
PW 413 Mop Star 130	•
PW 418	•
PW 5064	•
PW 5062	•
PW 5055	•
PW 5065	•
PW 5064 MOP STAR 60	•
PW 5070	•
PW 5082	•
PW 5084 MOP STAR 80	•
PW 5104 MOP STAR 100	•
PW 5105 Vario	•
PW 5134 MOP STAR 130	•
PW 6055	•
PW 6065	•
PW 6055 Vario	•
PW 6065 Vario	•
PW 6065 Plus	•
PW 6068 Plus	•
PW 6080	•
PW 6088	•
PW 6107	•
PW 6137	•
PW 5136	•
PW 6163	•
PW 6167	•
PW 6207	•
PW 6241	•
PW 6243	•
PW 6321	•
PW 6323	•
PW 811	•
PW 814	•
PW 818	•
PW 9055	•
PW 9065	•
PWT 6089	•
PWM 500-08	•
PWM 500-09	•
PWM 506 Mop Star 60	•
PWM 507	•
PWM 508 Mop Star 80	•
PWM 900-09	•
PWM 906	•
PWM 907	•
PWM 908	•

APWM 017

Dispenser pump rack

with slanted base for the complete residual emptying of liquid media containers.

EAN: 4002516501404 / Material number: 11933700 / Old Material Number: 59510017EU



PWM 511	•
PWM 909	•
PWM 514	•
PWM 520	•
PWM 912	•
PWM 916	•
PWM 920	•
PDW 909	•
Product category	
Dispenser system	•
Product characteristics	
Electrical connection	OHNE
Dimensions and weight	
External dimensions, net height in inches	40 9/16 (1030)
External dimensions, net width in inches	39 3/8 (1000)
External dimensions, net depth in inches	14 5/8 (371)
External dimensions, gross height in inches	45 3/8 (1152)
External dimensions, gross width in inches	51 3/16 (1300)
External dimensions, gross depth in inches	16 5/16 (413)
Net weight [lbs]	20 (9.00)
Gross weight in lbs	23 (10.00)