

## KFN 4799 DDE NA Freestanding fridge-freezer with DailyFresh, NoFrost, and IceMaker for fresh ice cubes any time.



- Large capacity drawer with moisture control DailyFresh
- Ice cubes thanks to the plumbed IceMaker
- No icing up of food and no need to defrost thanks to NoFrost
- Uniform temperature distribution inside the appliance DynaCool
- No visible build-up of condensation thanks to dry back wall

Appliance category	
Fridge-freezer	•
Design	
Free-standing	•
Door hinge side	right
Convertible hinging	•
Design	
Casing color	Silver
Front color	Stainless steel/CleanSteel
Type of lighting	LED
IceMaker lighting	•
User convenience	
Networking with Miele@home	•
Freshness system	DailyFresh
ComfortClean	•
DynaCool	•
NoFrost	•
DuplexCool	•
XL interior	•
VarioRoom	•
SoftClose door closing damper	•
IceMaker with plumbed water connection	•
Concealed door opener	EasyOpen lever handle
Control	
Electronic temperature display and control	SensorTouch
Precise adjustment	Fridge and freezer
	temperature
Fridge compartment can be switched off	Yes
Independent temperature control of fridge and freezer compartments	Yes
Super Cooling	•
SuperFrost	•
No. of temperature zones	2
Sabbath mode	•
Party mode	•
Holiday mode	•
Fridge/fridge zone	
No. of shelves	4
including number of split shelves (FlexiBoard)	 1
Chrome-plated metal bottle rack	•
No. of PerfectFresh drawers	1
Number of door racks for cans	3
Door rack for bottles	1
Door shelves	4
Freezer/freezer zone	
Number of freezer drawers	3
Safety	



# KFN 4799 DDE NA Freestanding fridge-freezer with DailyFresh, NoFrost, and IceMaker for fresh ice cubes any time.




Old Material Number: 38479940USA	
Acoustic door alarm	•
Acoustic temperature alarm, freezer section	•
Optical door alarm	•
Optical temperature alarm	•
Power cut indication for freezer compartment	•
Technical data	
Appliance width in in.(mm)	23 5/8 (600)
Appliance height in in.(mm)	79 3/8 (2015)
Appliance depth in in.(mm)	26 5/8 (675)
Weight in lbs.(kg)	184 (83.3)
Climatic classification	SN-T
Total usable capacity in cu. ft. (I)	13.21 (374)
Storage time in case of fault in h	20
Current consumption in milliampere (mA)	2300
Voltage in V	120
Fuse rating in A	10
Number of phases	1
Frequency in Hz	60
Wire length in ft (m)	6 (2.0)
Replacing bulbs	Customer Service
Standard accessories	
Egg rack	•

# Míele

#### KFN 4799 DDE NA


### Freestanding fridge-freezer

with DailyFresh, NoFrost, and IceMaker for fresh ice cubes any time.




KFN4799DDE, installation sketch (footnote\*) (installation drawings) (US)

\*To achieve the declared energy consumption, the spacers supplied with the unit must be used. This increases the depth of the unit by approx. 15 mm. The unit is fully functional without the use of the spacers, but has a slightly higher energy consumption.



KFN4799DDE, top view (installation drawings) (US)

\*To achieve the declared energy consumption, the spacers supplied with the unit must be used. This increases the depth of the unit by approx. 15 mm. The unit is fully functional without the use of the spacers, but has a slightly higher energy consumption.



 $\label{eq:KFN4799DDE} \textit{KFN4799DDE}, installation (footnote*) (installation drawings) (US)$ 

\*1. View from the front, 2. Mains connection cable, L = 2000 mm, 3. Water connection