

PWM 511 [EL DP DD SOM]

Professional washing machine, electric heating, drain pump and detergent drawer, M Touch Pro, for marine applications.



- Drum volume 3.53 (100) ft³ (l), maximum load size 25 (11.0) lb (kg)
- 14% less water consumption and 50% less energy consumption*
- Maximum user convenience with touch color display – M Touch Pro
- Perfect spinning results – residual moisture 50 %[†], g-factor370
- Connected for the future using LAN and WiFi

* Based on the Cottons program with a hot water connection, compared to the predecessor model.

† Residual moisture specification relates to a hot rinse during the last rinse cycle.

EAN: 4002516519775 / Material number: 11959810 / Old Material Number: 51511013SOM

Construction type and design	
Design	Front loader
Product line	Performance
Front	Iron Grey
Control panel color	Stainless Steel
Maximum load with a load ratio of 1:9 in lbs	25 (11.0)
Load ratio	1:9
Load in lbs	25 (11.0)
Drum volume in cubic feet (l)	3.53 (100)
Door opening [Ø] in in.(mm)	14 5/8 (370)
Door opening angle in degrees	180
Door hinging	right
Automatic door lock	•
Maintenance-free synchronous motor	•
Honeycomb drum	•
Application	
Suitable for off-shore use	•
Suitable for Marine use	•
Performance data	
Tested virucidal efficacy	•
Proven hygiene	•
Specific water consumption for cold water connection in gal/lb	7.10
Specific energy consumption for cold water connection in kWh/lb	0.12
Specific water consumption for hot water connection in l/kg	6.90
Specific energy consumption for hot water connection in kWh/lb	0.03
Water consumption for cold water connection in l	78.4
Energy consumption for cold water connection in kWh	1.37
Program duration in minutes with cold water connection	57
Water consumption for hot water connection in l	75.7
Energy consumption for hot water connection in kW	0.32
Program duration in minutes with hot water connection	52
Water consumption in ECO program for cold water connection in l	67.8
Energy consumption in ECO program for cold water connection in kWh	0.87
Program duration in minutes for ECO program with cold water connection	34
Water consumption in ECO program for hot water connection in l	68.3
Energy consumption in ECO program for hot water connection in kWh	0.13
Program duration in minutes for ECO program with hot water connection	33
Residual moisture with cold rinse in %	54
Residual moisture with hot rinse in %	50
Spin speed in rpm	1100
g factor	370
Tested operating hours	30000

PWM 511 [EL DP DD SOM]

Professional washing machine, electric heating, drain pump and detergent drawer, M Touch Pro, for marine applications.



EAN: 4002516519775 / Material number: 11959810 / Old Material Number: 51511013SOM

Control	
Control system	M Touch Pro
Programmability	programmable
Max. delay start in h	Can be selected freely
Countdown indicator	•
Program sequence indicator	•
Choice of display language	•
Standard/target group programs	
Basic programmes	•
Programmes for the hotel and catering industry	•
Programmes for retirement and care homes	•
Programmes for facility management	•
Programmes for laundrettes	•
Programmes for residential homes and apartments	•
Programmes for dry cleaners	•
Programmes for commercial laundries	•
Programmes for small businesses	•
Programmes for fire brigades and rescue services	•
Programmes for studs, riding schools, and stables	•
Programmes for universities, nurseries, and school	•
Programmes for hospitals	•
Programmes for fast food restaurants	•
Programmes for camp sites	•
Programmes for sports clubs	•
Programmes for beauty clinics, spas, and fitness studios	•
Programmes for domestic use	•
Programmes for doctors' and dentists' practices	•
Dispensing	
Detergent dispenser drawer	3 compartments
Flexible dispensing adapter (option)	•
Maximum number of connections for liquid dispenser pumps [number]	6
Empty sensor	•
Standard electrical connection	
Type of heating	Electric
Electrical connection	3 AC 440V 60HZ
Heater rating in kW	6.05
Total connected load in kW	6.30
Fuse rating in A	16
Possible voltage variant 1	
Electrical connection	3 AC 480V 60HZ
Heater rating in kW	7.20
Total connected load in kW	7.45
Fuse rating in A	16
Possible voltage variant 2	
Electrical connection	3 AC 400V 60 HZ
Heater rating in kW	5.00
Total connected load in kW	5.25
Fuse rating in A	16

PWM 511 [EL DP DD SOM]

Professional washing machine, electric heating, drain pump and detergent drawer, M Touch Pro, for marine applications.

EAN: 4002516519775 / Material number: 11959810 / Old Material Number: 51511013SOM

Water connection/drainage	
Cold water [number]	1x 1/2" hose w/ 3/4" th. union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union
Grey water (optional) [number]	1 x 1/2" w/ 3/4" union
Drain pump	DN 22
Dimensions and weight	
External dimensions, net height in inches	40 3/16 (1020)
External dimensions, net width in inches	27 9/16 (700)
External dimensions, net depth in inches	32 1/4 (818)
External dimensions, gross height in inches	47 13/16 (1214)
External dimensions, gross width in inches	29 9/16 (750)
External dimensions, gross depth in inches	36 1/8 (917)
Net weight in lbs.(kg)	340 (154.0)
Gross weight in lbs.	369 (167)
Maximum floor load in N/m ²	2636
Emission values	
Emissions – sound pressure at workplace	61 dB(A) re 20 µPa
Heat dissipation into the room in BTU/h	2.80
Features	
3-dimensional imbalance monitoring	•
Disinfection rinse	•
Temperature monitoring	•
Special heater element	•
Automatic load control Plus	•
Volumetric flow meter	•
Add laundry	•
Program selection via color frame	•
Appliance-independent accessories	•
Efficiency and sustainability	
Recycling rate in %	91
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak-load negotiation/energy management (optional)	•
LAN	•
WiFi	•
Connector Box	•
Capacities	
Synthetic duvets [number]	1
Synthetic pillows [number]	2
Feather duvets [number]	1
Feather pillows [number]	2
Standards, test certificates, and symbols	
CE	•
VDE-EMC	•
VDE	•
Splash protection IPX4	•
WEEE	•
EAC	•

PWM 511 [EL DP DD SOM]

Professional washing machine, electric heating, drain pump and detergent drawer, M Touch Pro, for marine applications.



EAN: 4002516519775 / Material number: 11959810 / Old Material Number: 51511013SOM

Complies with Machinery Directive 2006/42/EC

