

## PDR 910 [EL SOM]

Professional vented dryer, electric heating

with programmable M Touch Pro controls, for marine applications.



- Drum volume 6.36 (180.00) ft<sup>3</sup> (l), load size 18 (8.0) lb (kg) kg – 23 (10.0) lb (kg) kg
- Unique, gentle fabric care – patented honeycomb drum
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi
- Tested for intensive use – unique Miele quality

EAN: 4002516523352 / Material number: 11966850 / Old Material Number: 52910001SOM

<b>Construction type and design</b>	
Design	Front loader
Linie	Performance Plus
Front	Stainless Steel
Control panel color	Stainless Steel
Load in lbs.(kg)	23 (10.0)
Load size with a load ratio of 1:22.5	18 (8.0) lb (kg)
Load size with a load ratio of 1:18	23 (10.0) lb (kg)
Fill ratio	1:18
Drum volume in ft <sup>3</sup> (l)	6.36 (180.00)
Drying system	Exhaust air
Door opening [Ø] in in.(mm)	17 3/8 (440)
Door opening angle in degrees	180
Door hinging	left
Stainless steel honeycomb drum	Yes
<b>Application</b>	
Suitable for off-shore use	•
Suitable for Marine use	•
<b>Performance data</b>	
Maximum evaporation capacity in l/hour and gal. qts./hour	7 (7) gal (US)/min (l)
Specific energy consumption in kWh/kg an d kWh/p	0.51
Program cycle in min.	36
<b>Control</b>	
Control system	M Touch Pro
Programmability	programmable
Program controls	Residual moisture controlled
Max. delay start in h	24
Countdown indicator	•
Program sequence indicator	•
Choice of display language	•
<b>Standard electrical connection</b>	
Type of heating	Electric
Electrical connection	3N AC 400V 50/60HZ
Electric heater rating in kW	7.94
Total connected load in kW	8.20
Fuse rating in A	16
<b>Dimensions and weight</b>	
External dimensions, net height in inches	40 3/16 (1020)
External dimensions, net width in inches	27 9/16 (700)
External dimensions, net depth in inches	30 1/16 (763)
External dimensions, gross height in inches	47 7/8 (1215)
External dimensions, gross width in inches	29 15/16 (760)
External dimensions, gross depth in inches	32 5/16 (820)
Net weight in lbs. (kg)	159 (72.0)
Gross weight in lbs. (kg)	177 (80)
Maximum floor load in N/m <sup>2</sup>	853
<b>Emission values</b>	
Emissions – sound pressure at workplace	50 dB(A) re 20 µPa
Heat output to the room in Mj/h and BTUs /h	3.90

## PDR 910 [EL SOM]

Professional vented dryer, electric heating  
with programmable M Touch Pro controls, for marine applications.



EAN: 4002516523352 / Material number: 11966850 / Old Material Number: 52910001SOM

<b>Features</b>	
Intelligent drum reversal	•
Axial airflow	•
Large-surface filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Communication slot	•
Drum lighting	•
Program selection via color frame	•
Machine-independent accessories	•
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
<b>Capacities</b>	
Respirator masks [number]	4
Standard and target group programs	1
Over jackets [number]	2
Synthetic duvets [number]	1
Synthetic pillows [number]	2
Feather duvets [number]	1
Feather pillows [number]	2
Cloths, 22 g/0.8 oz [number]	182
Cotton mops, 40 cm [number]	42
Cotton mops, 50 cm [number]	36
Microfibre mops, 40 cm [number]	66
Microfibre mops, 50 cm [number]	47
Summer horse blankets [number]	2
<b>Standards, test certificates, and symbols</b>	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•
EAC	•
Complies with Machinery Directive 2006/42/EC	•