

PDR 910 [EL SOM]

Professional vented dryer, electric heating

with programmable M Touch Pro controls, for marine applications.



- Drum volume 6.36 (180.00) ft³ (l), load size 18 (8.0) lb (kg) kg – 23 (10.0) lb (kg) kg
- Unique, gentle fabric care – patented honeycomb drum
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi
- Tested for intensive use – unique Miele quality

EAN: 4002516523369 / Material number: 11966870 / Old Material Number: 52910012SOM

Construction type and design	
Design	Front loader
Linie	Performance Plus
Front	Stainless Steel
Control panel color	Stainless Steel
Load in lbs.(kg)	23 (10.0)
Load size with a load ratio of 1:22.5	18 (8.0) lb (kg)
Load size with a load ratio of 1:18	23 (10.0) lb (kg)
Fill ratio	1:18
Drum volume in ft ³ (l)	6.36 (180.00)
Drying system	Exhaust air
Door opening [Ø] in in.(mm)	17 3/8 (440)
Door opening angle in degrees	180
Door hinging	left
Stainless steel honeycomb drum	Yes
Application	
Suitable for off-shore use	•
Suitable for Marine use	•
Performance data	
Maximum evaporation capacity in l/hour and gal. qts./hour	7 (7) gal (US)/min (l)
Specific energy consumption in kWh/kg an d kWh/p	0.51
Program cycle in min.	44
Control	
Control system	M Touch Pro
Programmability	programmable
Program controls	Residual moisture controlled
Max. delay start in h	24
Countdown indicator	•
Program sequence indicator	•
Choice of display language	•
Standard electrical connection	
Type of heating	Electric
Electrical connection	3 AC 440V 50/60HZ
Electric heater rating in kW	5.18
Total connected load in kW	5.50
Fuse rating in A	10
Possible voltage variant 1	
Electrical connection	3 AC 480V 50/60HZ
Heater rating in kW	6.14
Total connected load in kW	6.40
Fuse rating in A	10
Possible voltage variant 2	
Electrical connection	3 AC 400V 50/60HZ
Heater rating in kW	4.26
Total connected load in kW	4.60
Fuse rating in A	10
Dimensions and weight	
External dimensions, net height in inches	40 3/16 (1020)
External dimensions, net width in inches	27 9/16 (700)

PDR 910 [EL SOM]

Professional vented dryer, electric heating

with programmable M Touch Pro controls, for marine applications.



EAN: 4002516523369 / Material number: 11966870 / Old Material Number: 52910012SOM

External dimensions, net depth in inches	30 1/16 (763)
External dimensions, gross height in inches	47 7/8 (1215)
External dimensions, gross width in inches	29 15/16 (760)
External dimensions, gross depth in inches	32 5/16 (820)
Net weight in lbs. (kg)	159 (72.0)
Gross weight in lbs. (kg)	177 (80)
Maximum floor load in N/m ²	853
Emission values	
Emissions – sound pressure at workplace	50 dB(A) re 20 µPa
Heat output to the room in Mj/h and BTUs /h	3.90
Features	
Intelligent drum reversal	•
Axial airflow	•
Large-surface filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Communication slot	•
Drum lighting	•
Program selection via color frame	•
Machine-independent accessories	•
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
Capacities	
Respirator masks [number]	4
Standard and target group programs	1
Over jackets [number]	2
Synthetic duvets [number]	1
Synthetic pillows [number]	2
Feather duvets [number]	1
Feather pillows [number]	2
Cloths, 22 g/0.8 oz [number]	182
Cotton mops, 40 cm [number]	42
Cotton mops, 50 cm [number]	36
Microfibre mops, 40 cm [number]	66
Microfibre mops, 50 cm [number]	47
Summer horse blankets [number]	2
Standards, test certificates, and symbols	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•
WEEE	•
EAC	•
Complies with Machinery Directive 2006/42/EC	•