

H 7280 BP
30 Inch Convection Oven
with clear text display, connectivity, and Self Clean.



- Clear-text display with sensor controls – DirectSensor S
- Minimal cleaning effort – Self-cleaning
- Achieve perfect results with ease – Automatic programs
- Unlimited possibilities – volume of 4.59 cu. ft. on 6 levels
- Network-enabled WiFi appliance – Miele@home

EAN: 4002516978602 / Material number: 11968200 /
Old Material Number: 22728025USA

| General information | |
|--|-----------------|
| Model number | H 7280 BP |
| Manufacturer material number | 11968200 |
| EAN number | 4002516978602 |
| Marketing class | Gold |
| Construction type and design | |
| VitroLine | • |
| Construction type and design | |
| Built-in wall oven | • |
| Color | Obsidian black |
| Convenience features | |
| Precise oven temperature regulation in °F (°C) | 85-575 (30-300) |
| Rapid PreHeat | • |
| Operating modes | |
| Defrost | • |
| Auto roast | • |
| Broil | • |
| Intensive | • |
| Surround | • |
| Bake | • |
| Convection Roast | • |
| Maxi Broil | • |
| Broiling operating modes | • |
| Automatic programs | • |
| User convenience | |
| Networking with Miele@home | • |
| Control panel | DirectSensor S |
| SoftOpen | • |
| SoftClose | • |
| MultiLingua | • |
| Time of day display | • |
| Time synchronization | • |
| Minute minder | • |
| Programming start of cooking duration | • |
| Programming end of cooking duration | • |
| Programmable cooking time | • |
| Actual temperature display | • |
| Audible signal when desired temperature is reached | • |
| Default temperature | • |
| Individual settings | • |
| Cleaning convenience | |
| Self-cleaning | • |
| CleanGlass door | • |
| Safety | |
| Appliance cooling system and cool touch front | • |
| Safety cut-out | • |
| System lock | • |
| Door lock during self cleaning | • |

H 7280 BP
30 Inch Convection Oven
with clear text display, connectivity, and Self Clean.



EAN: 4002516978602 / Material number: 11968200 /
Old Material Number: 22728025USA

| Technical data | |
|--|---|
| Cavity volume in cu.ft (l) | 4.59 (130) |
| No. of rack levels | 6 |
| Labeling of rack levels | • |
| Oven interior lighting | 2 halogen spots |
| TwinPower hot air fans | • |
| Plug type | NEMA plug: 14-30 |
| Niche width min. in inches (mm) | 28 5/8 (724) |
| Niche width max. in inches (mm) | 28 5/8 (724) |
| Niche height min. in inches (mm) | 28 3/8 (718) |
| Niche height max. in inches (mm) | 28 3/8 (718) |
| Niche depth in in. (mm) | 24 1/8 (610) |
| Weight in lbs. (kg) | 184.53 (83.7) |
| Total connected load in kW | 6.50 |
| Length of power cord in in. (m) | 1.80 |
| Power Rating in V | 120 |
| Voltage in V | 240/208 |
| Frequency in Hz | 60 |
| Fuse rating in A | 30 |
| Number of phases | 1 |
| Connection wire with plug | • |
| Standard accessories | |
| Universal tray with PerfectClean | 1 |
| Self Clean ready baking and roasting rack | 1 |
| Self Clean ready wire rack with rail system | 1 |
| Removable Self Clean-ready side racks (pair) | 1 |
| Available display languages | |
| Available display languages via MultiLingua | [?][?][?][?][?][?][?], [?][?], [?][?][?], deutsch, dansk, english, suomi, français, ελληνικά, italiano, [?][?][?], [?][?][?], hrvatski, bahasa malaysia, nederlands, norsk, polski, portuguais, română, русский, svenska, srpski, slovenčina, slovenščina, español, čeština, türkçe, українська, magyar |