

## PDR 918 [EL]

Professional vented dryer, electric heating

with programmable M Touch Pro controls for the maximum in flexibility.



- Drum volume 11.48 (325.00) ft<sup>3</sup> (l), load size 29 (13.0) lb (kg) – 40 (18.0) lb (kg)
- Unique, gentle fabric care – patented honeycomb drum
- Greatest energy efficiency thanks to Air Recycling
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi

EAN: 4002516546412 / Material number: 12012140 / Old Material Number: 52918023NAM

Construction type and design	
Design	Front loader
Linie	Performance Plus
Front	Stainless Steel
Load size with a load ratio of 1:25	29 (13.0) lb (kg)
Load size with a load ratio of 1:18	40 (18.0) lb (kg)
Drum volume in ft <sup>3</sup> (l)	11.48 (325.00)
Drying system	Exhaust air
Door opening [Ø] in in.(mm)	20 1/2 (520)
Door opening angle in degrees	180
Door hinging	left
Convertible hinging	•
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for fire brigades and rescue services	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas and fitness centers	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemical industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks and holiday complexes	•
Suitable for public/community care facilities	•
Performance data	
Maximum evaporation capacity in l/hour and gal. qts./hour	19 (19) gal (US)/min (l)
Program cycle in min.	24
Tested operating hours	20000
Control	
Control system	M Touch Pro
Programmability	programmable
Program controls	Residual moisture controlled
Max. delay start in h	24
Countdown indicator	•
Program sequence indicator	•
Choice of display language	•
Standard electrical connection	
Type of heating	Electric
Electrical connection	208/240 V 60 HZ 3 PH
Electric heater rating in kW	19.60
Total connected load in kW	20.50
Fuse rating in A	70

PDR 918 [EL]

Professional vented dryer, electric heating

with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516546412 / Material number: 12012140 / Old Material Number: 52918023NAM

<b>Dimensions and weight</b>	
External dimensions, net height in inches	55 1/8 (1400)
External dimensions, net width in inches	35 11/16 (906)
External dimensions, net depth in inches	40 3/4 (1035)
External dimensions, gross height in inches	60 1/8 (1526)
External dimensions, gross width in inches	42 15/16 (1090)
External dimensions, gross depth in inches	44 5/16 (1125)
Net weight in lbs. (kg)	383 (173.5)
Gross weight in lbs. (kg)	413 (187)
Maximum floor load in N/m <sup>2</sup>	2212
<b>Emission values</b>	
Emissions – sound pressure at workplace	50 dB(A) re 20 µPa
Heat output to the room in MJ/h and BTUs /h	4.50
<b>Features</b>	
Intelligent drum reversal	•
Axial airflow	•
Large-surface fluff filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecycling	•
Communication slot	•
Program selection via color frame	•
Emergency shut off	•
Machine-independent accessories	•
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
<b>Capacities</b>	
Respirator masks [number]	12
Standard and target group programs	2
Over jackets [number]	3
Synthetic duvets [number]	1
Synthetic pillows [number]	3
Feather duvets [number]	1
Feather pillows [number]	3
Cloths, 22 g/0.8 oz [number]	295
Cotton mops, 40 cm [number]	68
Cotton mops, 50 cm [number]	59
Microfibre mops, 40 cm [number]	108
Microfibre mops, 50 cm [number]	76
Summer horse blankets [number]	3
<b>Standards, test certificates, and symbols</b>	
Splash-proof safety rating IPX4	•
c ETL US	•
Complies with Machinery Directive 2006/42/EC	•