

PDR 522 ROP [SI]

Professional vented dryer, steam heating

with M Select ROP residual moisture control for perfect drying results.



- Drum volume 14.13 (400.00) ft³ (l), load size 36 (16.0) lb (kg) – 49 (22.0) lb (kg)
- Unique, gentle fabric care – patented honeycomb drum
- Greatest energy efficiency thanks to Air Recycling
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi

EAN: 4002516546481 / Material number: 12012270 / Old Material Number: 52522018NAM

Construction type and design	
Design	Front loader
Linie	Performance
Front	Iron Grey
Load size with a load ratio of 1:25	36 (16.0)
Load size with a load ratio of 1:18	50 (22.5)
Drum volume in ft ³ (l)	14.13 (400.00)
Drying system	Exhaust air
Door opening [Ø] in in.(mm)	20 1/2 (520)
Door opening angle in degrees	180
Door hinging	left
Convertible hinging	•
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas and fit ness centers	•
Suitable for amusement parks and holiday complexes	•
Suitable for public/community care facilities	•
Performance data	
Maximum evaporation capacity in l/hour and gal. qts./hour	21 (21) gal (US)/min (l)
Specific energy consumption in kWh/kg an d kWh/p	0.61
Program cycle in min.	26
Tested operating hours	20000
Control	
Control system	M Select Benchmark
Programmability	Setting of defined parameters
Program controls	Residual moisture controlled
Max. delay start in h	24
Countdown indicator	•
Fascia panel with easy-to-understand sym bols	•
Standard electrical connection	
Type of heating	Indirect steam
Electrical connection	208/240 V 60 HZ 2 PH
Electric heater rating in kW	0.00
Steam heater rating in kW	28.00
Total connected load in kW	1.00
Fuse rating in A	15
Dimensions and weight of dryer	
External dimensions, net height in inches	55 1/8 (1400)
External dimensions, net width in inches	35 11/16 (906)

PDR 522 ROP [SI]

Professional vented dryer, steam heating

with M Select ROP residual moisture control for perfect drying results.



EAN: 4002516546481 / Material number: 12012270 / Old Material Number: 52522018NAM

External dimensions, net depth in inches	45 3/4 (1162)
External dimensions, gross height in inches	60 1/8 (1526)
External dimensions, gross width in inches	42 15/16 (1090)
External dimensions, gross depth in inches	49 3/8 (1254)
Net weight in lbs. (kg)	512 (231.9)
Gross weight in lbs. (kg)	543 (246)
Maximum floor load in N/m ²	2600
Emission values	
Emissions – sound pressure at workplace	61 dB(A) re 20 µPa
Heat output to the room in Mj/h and BTUs /h	2.60
Features	
Intelligent drum reversal	•
Axial airflow	•
Large-surface fluff filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecycling	•
Communication slot	•
Program selection via color frame	•
Emergency shut off	•
Machine-independent accessories	•
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
Capacities	
Cloths, 22 g/0.8 oz [number]	364
Summer horse blankets [number]	3
Standards, test certificates, and symbols	
Splash-proof safety rating IPX4	•
c ETL US	•
Complies with Machinery Directive 2006/42/EC	•