

## PDR 922 [HW]

Professional vented dryer, heated with hot water  
with programmable M Touch Pro controls for the maximum in flexibility.



- Drum volume 14.13 (400.00) ft<sup>3</sup> (l), load size 29 (13.0) lb (kg) kg – 36 (16.0) lb (kg)
- Unique, gentle fabric care – patented honeycomb drum
- Greatest energy efficiency thanks to Air Recycling Plus
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi

EAN: 4002516546535 / Material number: 12012310 /  
Old Material Number: 52922029NAM

<b>Construction type and design</b>	
Design	Front loader
Linie	Performance Plus
Front	Stainless Steel
Load size with a load ratio of 1:32	29 (13.0) lb (kg)
Load size with a load ratio of 1:25	36 (16.0)
Load size with a load ratio of 1:18	50 (22.5)
Drum volume in ft <sup>3</sup> (l)	14.13 (400.00)
Drying system	Hot water
Door opening [Ø] in in.(mm)	20 1/2 (520)
Door opening angle in degrees	180
Door hinging	left
Convertible hinging	•
Stainless steel honeycomb drum	Yes
<b>Application</b>	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for fire brigades and rescue services	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas and fit ness centers	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemical industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks and holiday complexes	•
Suitable for public/community care facilities	•
<b>Performance data</b>	
Maximum evaporation capacity in l/hour and gal. qts./hour	11 (11) gal (US)/min (l)
Specific energy consumption in kWh/kg an d kWh/p	0.59
Program cycle in min.	60
Tested operating hours	20000
<b>Control</b>	
Control system	M Touch Pro
Programmability	programmable
Program controls	Residual moisture controlled
Max. delay start in h	24
Countdown indicator	•
Program sequence indicator	•
Choice of display language	•
<b>Standard electrical connection</b>	
Type of heating	Hot water
Electrical connection	208/240 V 60 HZ 2 PH

## PDR 922 [HW]

Professional vented dryer, heated with hot water  
with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516546535 / Material number: 12012310 /  
Old Material Number: 52922029NAM

Heater rating, hot water in kW	9.80
Total connected load in kW	1.00
Fuse rating in A	15

### Dimensions and weight of dryer

External dimensions, net height in inches	55 1/8 (1400)
External dimensions, net width in inches	35 11/16 (906)
External dimensions, net depth in inches	45 3/4 (1162)
External dimensions, gross height in inches	60 1/8 (1526)
External dimensions, gross width in inches	42 15/16 (1090)
External dimensions, gross depth in inches	49 3/8 (1254)
Net weight in lbs. (kg)	512 (231.9)
Gross weight in lbs. (kg)	543 (246)
Maximum floor load in N	2600

### Emission values

Emissions – sound pressure at workplace	62 dB(A) re 20 µPa
Heat output to the room in Mj/h and BTUs /h	2.60

### Features

Intelligent drum reversal	•
Axial airflow	•
Large-surface fluff filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecycling	•
Communication slot	•
Program selection via color frame	•
Emergency shut off	•
Machine-independent accessories	•

### Efficiency and sustainability

Recycling rate in %	91
---------------------	----

### Connection options

Payment system (optional)	•
Optical interface for service access	•
Peak-load negotiation / energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•

### Capacities

Respirator masks [number]	16
Standard and target group programs	2
Over jackets [number]	3
Synthetic duvets [number]	1
Synthetic pillows [number]	3
Feather duvets [number]	2
Feather pillows [number]	4
Cloths, 22 g/0.8 oz [number]	364
Cotton mops, 40 cm [number]	84
Cotton mops, 50 cm [number]	73
Microfibre mops, 40 cm [number]	133

PDR 922 [HW]

Professional vented dryer, heated with hot water  
with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516546535 / Material number: 12012310 /  
Old Material Number: 52922029NAM

Microfibre mops, 50 cm [number]	94
---------------------------------	----

Summer horse blankets [number]	3
--------------------------------	---

<b>Standards, test certificates, and symbols</b>	
--	--

Splash-proof safety rating IPX4	•
---------------------------------	---

c ETL US	•
----------	---

Complies with Machinery Directive 2006/42/EC	•
--	---