

PDR 928 [SI]

Professional vented dryer, steam heating
with programmable M Touch Pro controls for the maximum in flexibility.



- Drum volume 17.66 (500.00) ft³ (l), load size 45 (20.0) lb (kg) – 62 (28.0) lb (kg)
- Unique, gentle fabric care – patented honeycomb drum
- Greatest energy efficiency thanks to Air Recycling
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi

EAN: 4002516546542 / Material number: 12012320 / Old Material Number: 52928020NAM

Construction type and design	
Design	Front loader
Linie	Performance Plus
Front	Stainless Steel
Load size with a load ratio of 1:25	45 (20.0)
Load size with a load ratio of 1:18	60 (27.0)
Drum volume in ft ³ (l)	17.66 (500.00)
Drying system	Exhaust air
Door opening [Ø] in in.(mm)	20 1/2 (520)
Door opening angle in degrees	180
Door hinging	left
Convertible hinging	•
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for fire brigades and rescue services	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas and fitness centers	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemical industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks and holiday complexes	•
Suitable for public/community care facilities	•
Performance data	
Maximum evaporation capacity in l/hour and gal. qts./hour	26 (26) gal (US)/min (l)
Specific energy consumption in kWh/kg and kWh/p	0.59
Program cycle in min.	25
Tested operating hours	20000
Control	
Control system	M Touch Pro
Programmability	programmable
Program controls	Residual moisture controlled
Max. delay start in h	24
Countdown indicator	•
Program sequence indicator	•
Choice of display language	•
Standard electrical connection	
Type of heating	Indirect steam
Electrical connection	208/240 V 60 HZ 2 PH
Electric heater rating in kW	0.00
Steam heater rating in kW	35.00

PDR 928 [SI]

Professional vented dryer, steam heating

with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516546542 / Material number: 12012320 / Old Material Number: 52928020NAM

Total connected load in kW	1.20
Fuse rating in A	15
Dimensions and weight of dryer	
External dimensions, net height in inches	64 5/8 (1640)
External dimensions, net width in inches	47 1/2 (1206)
External dimensions, net depth in inches	40 1/8 (1019)
External dimensions, gross height in inches	69 9/16 (1766)
External dimensions, gross width in inches	54 3/4 (1390)
External dimensions, gross depth in inches	43 5/8 (1108)
Net weight in lbs. (kg)	621 (281.3)
Gross weight in lbs. (kg)	653 (296)
Maximum floor load in N/m ²	3417
Emission values	
Emissions – sound pressure at workplace	60 dB(A) re 20 µPa
Heat output to the room in Mj/h and BTUs /h	3.30
Features	
Intelligent drum reversal	•
Axial airflow	•
Large-surface fluff filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecycling	•
Communication slot	•
Program selection via color frame	•
Emergency shut off	•
Machine-independent accessories	•
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak load cut-out/energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•
Capacities	
Respirator masks [number]	12
Standard and target group programs	3
Over jackets [number]	5
Synthetic duvets [number]	2
Synthetic pillows [number]	3
Feather duvets [number]	2
Feather pillows [number]	5
Cloths, 22 g/0.8 oz [number]	545
Cotton mops, 40 cm [number]	105
Cotton mops, 50 cm [number]	91
Microfibre mops, 40 cm [number]	167
Microfibre mops, 50 cm [number]	118
Summer horse blankets [number]	3
Standards, test certificates, and symbols	
Splash-proof safety rating IPX4	•
c ETL US	•
Complies with Machinery Directive 2006/42/EC	•

PDR 928 [SI]

Professional vented dryer, steam heating
with programmable M Touch Pro controls for the maximum in flexibility.