

PDR 528 ROP [EL]

Professional vented dryer, electric heating

with M Select ROP residual moisture control for perfect drying results.



- Drum volume 17.66 (500.00) ft³ (l), load size 45 (20.0) lb (kg) – 62 (28.0) lb (kg)
- Unique, gentle fabric care – patented honeycomb drum
- Greatest energy efficiency thanks to Air Recycling
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi

EAN: 4002516546566 / Material number: 12012340 / Old Material Number: 52528007NAM

| Construction type and design | |
|---|-------------------------------|
| Design | Front loader |
| Linie | Performance |
| Front | Stainless Steel |
| Load size with a load ratio of 1:25 | 45 (20.0) |
| Load size with a load ratio of 1:18 | 60 (27.0) |
| Drum volume in ft ³ (l) | 17.66 (500.00) |
| Drying system | Exhaust air |
| Door opening [Ø] in in.(mm) | 20 1/2 (520) |
| Door opening angle in degrees | 180 |
| Door hinging | left |
| Convertible hinging | • |
| Stainless steel honeycomb drum | Yes |
| Application | |
| Suitable for the hotel and catering industry | • |
| Suitable for retirement and care homes | • |
| Suitable for facility management | • |
| Suitable for commercial laundries | • |
| Suitable for studs, riding schools and stables | • |
| Suitable for universities, nurseries, and schools | • |
| Suitable for hospitals | • |
| Suitable for sports clubs | • |
| Suitable for beauty salons, spas and fit ness centers | • |
| Suitable for amusement parks and holiday complexes | • |
| Suitable for public/community care facilities | • |
| Performance data | |
| Maximum evaporation capacity in l/hour and gal. qts./hour | 27 (27) gal (US)/min (l) |
| Specific energy consumption in kWh/kg an d kWh/p | 0.59 |
| Program cycle in min. | 24 |
| Tested operating hours | 20000 |
| Control | |
| Control system | M Select Benchmark |
| Programmability | Setting of defined parameters |
| Program controls | Residual moisture controlled |
| Max. delay start in h | 24 |
| Countdown indicator | • |
| Fascia panel with easy-to-understand sym bols | • |
| Standard electrical connection | |
| Type of heating | Electric |
| Electrical connection | 208/240 V 60 HZ 3 PH |
| Electric heater rating in kW | 29.40 |
| Total connected load in kW | 30.60 |
| Fuse rating in A | 100 |
| Dimensions and weight of dryer | |
| External dimensions, net height in inches | 64 5/8 (1640) |
| External dimensions, net width in inches | 47 1/2 (1206) |
| External dimensions, net depth in inches | 40 1/8 (1019) |
| External dimensions, gross height in inches | 69 9/16 (1766) |

PDR 528 ROP [EL]

Professional vented dryer, electric heating

with M Select ROP residual moisture control for perfect drying results.



EAN: 4002516546566 / Material number: 12012340 / Old Material Number: 52528007NAM

| | |
|--|--------------------|
| External dimensions, gross width in inches | 54 3/4 (1390) |
| External dimensions, gross depth in inches | 43 5/8 (1108) |
| Net weight in lbs. (kg) | 537 (243.3) |
| Gross weight in lbs. (kg) | 569 (258) |
| Maximum floor load in N/m ² | 3044 |
| Emission values | |
| Emissions – sound pressure at workplace | 58 dB(A) re 20 µPa |
| Heat output to the room in Mj/h and BTUs /h | 3.30 |
| Features | |
| Intelligent drum reversal | • |
| Axial airflow | • |
| Large-surface fluff filter | • |
| PerfectDry | • |
| SoftLift drum ribs | • |
| AirRecycling | • |
| Communication slot | • |
| Program selection via color frame | • |
| Emergency shut off | • |
| Machine-independent accessories | • |
| Connection options | |
| Payment system (optional) | • |
| Optical interface for service access | • |
| Peak load cut-out/energy management (optional) | • |
| WiFi tumble dryer | • |
| Connector Box | • |
| LAN module (optional) | • |
| Capacities | |
| Cloths, 22 g/0.8 oz [number] | 545 |
| Summer horse blankets [number] | 3 |
| Standards, test certificates, and symbols | |
| Splash-proof safety rating IPX4 | • |
| c ETL US | • |
| Complies with Machinery Directive 2006/42/EC | • |