

G 7566 SCVi XXL SF AutoDos
Fully integrated dishwasher XXL
with Automatic Dispensing thanks to AutoDos with integrated PowerDisk.



- ExtraComfort Baskets w/3D MultiFlex Tray adjusts for more volume
- Miele@home w/ AutoStart, remotely program your dishwasher
- QuickIntenseWash, superior cleaning and drying in under 60 min
- Perfect illumination for easy loading – BrilliantLight
- Clean Touch Steel front with handle in ContourLine design

EAN: 4002516569169 / Material number: 12055110 / Old Material Number: 21756665USA

Type	
Fully integrated dishwashers	•
24 inch dishwasher	•
Design	
Fascia color	Clean Touch Steel/Obsidian Black
Fascia panel version	Fully integrated fascia
Control type	Softkeys
Control panel	1-line display with plain text
Display color	White
MultiLingua	•
Convenience	
Networking with Miele@home	•
Automatic dispensing with PowerDisk	•
Door closing aid	ComfortClose
LED Lighting	•
Operating noise dB(A) re 1 pW	40
Countdown indicator	•
Delay start up to 24 hours	•
In-operation indication	Display
Display language selection	•
Efficiency and sustainability	
EcoFeedback	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
ENERGY STAR® Most Efficient	•
Quality of results	
Fresh water dishwasher	•
SensorDry	•
Active condensation drying	•
Perfect GlassCare	•
Wash programs	
QuickIntenseWash	•
Economy	•
Normal	•
SensorWash	•
Pots & Pans	•
IntenseWash	•
China & Crystal	•
SaniWash	•
Energy Saver	•
Extra Quiet 39 dB(A)	•
Glasses – No Rinse Aid	•
Appliance care	•
Rinse & Hold	•
Dishwashing options	
AutoDos	•
IntenseZone	•

G 7566 SCVi XXL SF AutoDos
Fully integrated dishwasher XXL
with Automatic Dispensing thanks to AutoDos with integrated PowerDisk.



EAN: 4002516569169 / Material number: 12055110 / Old Material Number: 21756665USA

Express	•
Extra Clean	•
Extra dry	•
Baskets	
Cutlery loading	3D MultiFlex Tray
FlexCare glass holder	4
FlexCare cup rack	2
Basket design	MaxiComfort
Safety	
Waterproof system	•
Check filter saturation indicator	•
Child Safety lock	•
Technical data	
Niche width min in in.(mm)	23 5/8 (600)
Niche width max in in.(mm)	23 5/8 (600)
Niche height min in in.(mm)	33 3/4 (855)
Niche height max in in.(mm)	36 1/4 (920)
Niche depth in in.(mm)	22 1/2 (570)
Appliance width in in.(mm)	23 5/8 (598)
Appliance height in in.(mm)	33 3/4 (855)
Appliance depth in in.(mm)	23 5/8 (600)
Appliance depth with door open in in.(cm)	47 1/2 (120.5)
Net weight in lbs. (kg)	122 (55.0)
Total connected load in kW	1.40
Voltage in V	120
Fuse rating in A	15
Number of phases	1
Electrical frequency standard	60
Length of water inlet hose in ft (m)	5 (1.50)
Length of water drain hose in ft (m)	5 (1.50)
Length of electrical wire in ft (m)	4 (1.20)
Replacing bulbs	Customer Service
Available display languages	
Available display languages via MultiLingua	deutsch, english, español, français, portugês,
Standard accessories	
1 x PowerDisk	•
Voucher for 6 x PowerDisk	•