

## PFD 404 U [208V]

Built-under fresh water dishwasher

w/ baskets for care homes, nursery schools and people w/ hygiene requirements.



- Max. cleaning performance\*: 380 plates/h or 20 baskets/h
- First-class results thanks to fresh water system
- Extremely hygienic results – final rinse temperature of 185 (85) °F (°C)
- Safe and easy operation – automatic door opening
- Max. user convenience with M Touch Flex full-touch color display

\* Depending on site conditions (temperature of incoming water / power connection) values given may vary.

EAN: 4002516577348 / Material number: 12066570 / Old Material Number: 61040430NAM

Construction type and design	
Model	Built-under dishwasher
Range	MasterLine
Model	Hygiene
Wash system	Fresh water front loader
Number of levels	2
Front	Stainless steel
Lid	Without lid
Side walls	Galvanised
Application	
Suitable for retirement and care homes	•
Suitable for hospitals	•
Suitable for child care facilities	•
Suitable for universities and schools	•
Performance data	
Tested virucidal efficacy	•
Certified hygiene	•
Circulation pump, Qmax in gal/min (l/min)	103 (390)
Shortest program duration in min.	6
Maximum final rinse temperature in °F (°C)	185 (85)
Cleaning performance, plates/h	380
Cleaning performance, baskets/h	20
Possible to wash plastic baskets on two levels	•
Service life in wash cycles	28000
Control	
Control system	M Touch Flex
Max. delay start in h	24
Countdown indicator	•
Programs [quantity]	12
Program sequence indicator	•
Choice of display language	•
Language-neutral operation	•
Standard electrical connection	
Electrical connection	2 AC 208V 60HZ
Heater rating in kW	5.40
Total connected load in kW	5.80
Fuse rating in A	30
Length of power cord in ft (m)	6 (1.90)
NEMA plug: Twist Lock L6-30	•
Possible voltage variant 1	
Electrical connection	3 AC 208V 60HZ
Heater rating in kW	5.40
Total connected load in kW	5.80
Fuse rating in A	20
Water connection/drainage	
Cold water [number]	1
Hot water [number]	1
Required flow pressure in bar	1.00-10.00
Drain hose [DN]	22
Maximum delivery head for drain pump in inches (cm)	39 3/8 (100)

## PFD 404 U [208V]

Built-under fresh water dishwasher

w/ baskets for care homes, nursery schools and people w/ hygiene requirements.



EAN: 4002516577348 / Material number: 12066570 / Old Material Number: 61040430NAM

Integrated water softener	•
Maximum water hardness in gpg (mmol/l)	62.59 (10.70)
Water protection system	Waterproof system
Water consumption per wash cycle in gal (l)	2.1 (8.00) gll (l)
Length of water inlet hose in inches (cm)	67 (170)
Length of water drain hose in inches (cm)	59 1/8 (150)
<b>Dimensions and weight</b>	
External dimensions, net height in inches	32 5/16 (820)
External dimensions, net width in inches	23 9/16 (598)
External dimensions, net depth in inches	23 7/16 (595)
External dimensions, gross height in inches	36 1/4 (920)
External dimensions, gross width in inches	26 7/16 (670)
External dimensions, gross depth in inches	29 3/16 (740)
Usable space in wash cabinet, width in inches (mm)	22 1/16 (559)
Usable space in wash cabinet, height in inches (mm)	21 1/8 (536)
Usable space in wash cabinet, depth of upper basket in inches (mm)	18 11/16 (474)
Usable space in wash cabinet, depth of lower basket in inches (mm)	20 3/8 (516)
In-feed height above floor in inches (mm)	8 9/16 (216)
Required niche width in mm	23 5/8 (600)
Net weight [kg]	166 (75)
Gross weight in lbs.	188 (85)
Maximum floor load in N/m <sup>2</sup>	1200
<b>Emission values</b>	
Emission sound pressure level in workplace (LpA)	45 dB(A) re 20 µPa
Sound power (LwA) in dB(A) re 1 pW	57.0
Heat output to the room in Mj/h	1.44
<b>Programs</b>	
Universal	•
Super short	•
Short	•
SaniWash	•
SaniWash Plus	•
Cold/Pre-wash	•
Glasses	•
Beer glasses	•
Cutlery	•
Plastic	•
Intensive	•
Reactivation	•
Drainage by pump	•
<b>Baskets</b>	
2 x E 816 inserts for plates	•
1 x APFD 215 upper basket	•
1 x APFD 220 lower basket for inserts	•
2 x APFD 420 insert for cutlery	•
Height-adjustable upper basket	•
Combinable with APFD 210 bottle basket	•
<b>Features</b>	
Drying	AutoOpen assisted drying

## PFD 404 U [208V]

Built-under fresh water dishwasher

w/ baskets for care homes, nursery schools and people w/ hygiene requirements.



EAN: 4002516577348 / Material number: 12066570 / Old Material Number: 61040430NAM

1 Combi dispenser/door for powder and liquid media	•
Wash cabinet made from high-quality stainless steel	•
In-door salt container	•
AutoClose	•
Perfect GlassCare	•
Aerosol steam condenser	•
Door lock, protected by code	•
Adjustable temperature holding time	•
Adjustable final rinse temperature	•
Optical interface	•
Highly effective filter system with filter monitoring	•
A wide range of accessories (optional)	•
<b>Connection options</b>	
External dispensing module for liquid cleaning agent	•
<b>Standards, test certificates, and symbols</b>	
Complies with Machinery Directive 2006/42/EC	•
Splash protection IPX1	•
EMC radio suppressed	•
DIN 10512	•
DIN EN 17735	•
ETL	•
ADA compliant	•