

KM 7720 FR

24-inch induction cooktop, operated with its own controls
with 3 round cooking zones



- Intuitive quick selection via number sequences – Smart Select
- Versatile – 3 cooking zones, 1 extra large with diameter of 11 in
- With a width of 24 3/4 (626) in (mm) and stainless steel frame for proud-mounting
- Shortest heating-up times – TwinBooster
- Communication with the ventilation hood – automatic Con@ctivity function

EAN: 4002516611547 / Material number: 12074190 /
Old Material Number: 26772000USA

Heating type	
Fuel type	Induction
Design	
Independent of oven	•
Design	
Elegant glass ceramic surface	•
Surface-mounted/flush-fit	–/–
Ceramic surface color	Black
All-round stainless-steel frame	•
Proud installation	•
Cooking zone details	
No. of rings	3
Number of cooking areas	0
Maximum number of pans	3
1st cooking zone/cooking area	
Position	left center
Type	Variable cooking zone
Size in mm	Ø 180-280
Max. Booster power rating in W	3000
Max. rating in W	2600
Max. TwinBooster power rating in W	3700
2nd cooking zone/cooking area	
Position	rear right
Type	Variable cooking zone
Size in mm	Ø 140-200
Max. Booster power rating in W	2500
Max. rating in W	1850
Max. TwinBooster power rating in W	3000
3rd cooking zone/cooking area	
Position	front right
Type	Variable cooking zone
Size in mm	Ø 100-160
Max. Booster power rating in W	1700
Max. rating in W	1400
Max. TwinBooster power rating in W	2200
User convenience	
Networking with Miele@home	•
Automatic function	Con@ctivity 3.0
Pan and pan size recognition	•
Operation via touchpad sensors	Smart Select
Display color	Yellow
Permanent pan recognition	•
Stop & Go function	•
Wipe protection	•
Recall function	•
Minute minder	•
Automatic switch-off for all rings	•
AutoBoost	•

KM 7720 FR

24-inch induction cooktop, operated with its own controls
with 3 round cooking zones




EAN: 4002516611547 / Material number: 12074190 /
Old Material Number: 26772000USA

Keep-warm function	•
Individual setting options (e.g. acoustic signal tones)	•
Cleaning convenience	
Easy to clean ceramic glass	•
Safety	
Safety cut-out	•
Lock function	•
System lock	•
Integrated cooling blower	•
Overheating protection	•
Residual heat indicator	•
Technical data	
Dimensions (width) in in. (mm)	24 3/4 (626)
Dimensions (height) in in. (mm)	3 1/8 (78)
Dimensions in mm (depth)	21 1/2 (544)
Cutout dimensions (width) in in. (mm)	22 3/8 in (567 mm)
Cutout dimensions (depth) in in. (mm)	20 1/2 in (518 mm)
Casing height incl. connection box in mm	2 7/8 (71)
Weight in lbs. (kg)	30 (14)
Total connected load in kW	6.60-7.60
Power cord length in in. (m)	3 (1.2)
Voltage in V	208-240
Frequency in Hz	50-60
Standard accessories	
Power cord	Yes

KM 7720 FR

24-inch induction cooktop, operated with its own controls
with 3 round cooking zones



KM7720FR – with frame, surface mounted overlying
installation (*footnote) – drawing

① Front, ② Flexible metal hose with power cords, L = 4'
(1,200) mm,