

PWM 916 [SI DV DD]

Professional washing machine, steam heating (indirect)
with detergent drawer, M Touch Pro Plus – freely programmable.



- Drum volume 4.94 (140) ft³ (l), load size 35 (15.5) lb (kg)
- Top cleaning & consumption values – innovative Miele technology
- Ideal operation thanks to touch color display – M Touch Pro Plus
- Simple and safe operation thanks to automatic door lock
- Connected for the future using LAN and WiFi

EAN: 4002516582441 / Material number: 12084550 / Old Material Number: 51916032NAM

Construction type and design	
Design	Front loader
Product line	Performance Plus
Front	Stainless Steel
Control panel color	Stainless Steel
Maximum load with a load ratio of 1:9 in lbs	36 (16.0)
Load ratio	1:9
Load in lbs	35 (15.5)
Drum volume in cubic feet (l)	4.94 (140)
Door opening [Ø] in in.(mm)	16 3/8 (415)
Door opening angle in degrees	180
Door hinging	right
Automatic door lock	•
Innovative suds container	•
Maintenance-free motor with frequency converter	•
Patented honeycomb drum 2.0	•
Application	
Suitable for the hotel and catering industry	•
Suitable for senior living facilities	•
Suitable for facility management	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for fire brigades and rescue services	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centers	•
Suitable for the petrochemical industry	•
Suitable for amusement parks and holiday complexes	•
Suitable for public/community care facilities	•
Performance data	
Tested virucidal efficacy	•
Proven hygiene	•
Specific water consumption for cold water connection in gal/lb	6.20
Specific energy consumption for cold water connection in kWh/lb	0.14
Specific water consumption for hot water connection in l/kg	5.90
Specific energy consumption for hot water connection in kWh/lb	0.06
Water consumption for cold water connection in l	99.2
Water consumption for cold water connection in Mops standard program in gal	182.2
Energy consumption for cold water connection in kWh	2.26
Energy consumption for cold water connection in Mops standard program in kWh	3.21
Program duration in minutes with cold water connection	46
Water consumption for hot water connection in l	94.4

PWM 916 [SI DV DD]

Professional washing machine, steam heating (indirect)
with detergent drawer, M Touch Pro Plus – freely programmable.



EAN: 4002516582441 / Material number: 12084550 / Old Material Number: 51916032NAM

Water consumption for hot water connection in Mops standard program in gal	178.1
Energy consumption for hot water connection in kW	0.96
Energy consumption for hot water connection in Mops standard program in kWh	1.33
Program duration in minutes with hot water connection	43
Water consumption in ECO program for cold water connection in l	92.8
Energy consumption in ECO program for cold water connection in kWh	1.48
Program duration in minutes for ECO program with cold water connection	33
Water consumption in ECO program for hot water connection in l	91.2
Energy consumption in ECO program for hot water connection in kWh	0.48
Program duration in minutes for ECO program with hot water connection	32
Program runtime in minutes for Mops standard program with cold water connection	50
Program runtime in minutes for Mops standard program with hot water connection	47
Residual moisture with cold rinse in %	48
Residual moisture with hot rinse in %	44
Residual moisture when processing cleaning cloths in %	25
Spin speed in rpm	1075
g factor	462
Tested operating hours	30000
Control	
Control system	M Touch Pro Plus
Programmability	Freely programmable
Max. delay start in h	Can be selected freely
Countdown indicator	•
Program sequence indicator	•
Choice of display language	•
Option to enter weight prior to start of program	•
Standard/target group programs	
Basic programmes	•
Dispensing	
Detergent dispenser drawer	3 compartments
Maximum number of connections for liquid dispenser pumps [number]	12
Empty sensor	•
Standard electrical connection	
Type of heating	Indirect steam
Electrical connection	208/240 V 60 HZ 3 PH
Steam heater rating in kW	37.00
Total connected load in kW	2.30
Fuse rating in A	15
Water connection/drainage	
Cold water [number]	3 x 1/2" hose w/ 3/4" union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union

PWM 916 [SI DV DD]

Professional washing machine, steam heating (indirect)

with detergent drawer, M Touch Pro Plus – freely programmable.

EAN: 4002516582441 / Material number: 12084550 / Old Material Number: 51916032NAM

Hard water (optional) [number]	2 x 1/2" w/ 3/4" union
Dump valve	DN 70
Steam connection	
Steam connection	2 x 1/2"
Dimensions and weight	
External dimensions, net height in inches	57 1/8 (1450)
External dimensions, net width in inches	36 7/16 (924)
External dimensions, net depth in inches	37 9/16 (954)
External dimensions, gross height in inches	62 7/16 (1585)
External dimensions, gross width in inches	47 11/16 (1210)
External dimensions, gross depth in inches	44 1/2 (1130)
Net weight in lbs.(kg)	845 (383.0)
Gross weight in lbs.	896 (406)
Maximum floor load in N/m ²	5504
Emission values	
Emissions – sound pressure at workplace	65 dB(A) re 20 µPa
Heat dissipation into the room in BTU/h	6.48
Features	
Patented preliminary drainage	•
Patented cleaning cloth program	•
3-dimensional imbalance monitoring	•
Disinfection rinse	•
Efficient scoop-and-ladle ribs	•
EcoSpeed	•
Spring-in-spring system	•
Temperature monitoring	•
Automatic load control Plus	•
Volumetric flow meter (optional)	•
Add laundry	•
Program selection via color frame	•
Emergency shut off	•
Appliance-independent accessories	•
Efficiency and sustainability	
Recycling rate in %	92
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak-load negotiation/energy management (optional)	•
Water recovery (optional)	•
LAN	•
WiFi	•
Connector Box	•
Capacities	
Respirator masks [number]	13
Helmets [number]	4
Overalls [number]	2
Over jackets [number]	3
Chemical protection overalls [number]	1
Synthetic duvets [number]	1
Synthetic pillows [number]	3
Feather duvets [number]	1

PWM 916 [SI DV DD]

Professional washing machine, steam heating (indirect)
with detergent drawer, M Touch Pro Plus – freely programmable.



EAN: 4002516582441 / Material number: 12084550 / Old Material Number: 51916032NAM

Feather pillows [number]	3
Cloths, 22 g/0.8 oz[number]	355
Cotton mops, 40 cm/15.7 in[number]	82
Cotton mops, 50 cm/19.7 in[number]	71
Microfibre mops, 40 cm/15.7 in [number]	130
Microfibre mops, 50 cm/19.7 in [number]	91
Mops, office, 100 g [quantity]	160
Mops, stairway, 150 g [quantity]	105
Summer horse blankets [number]	3
Standards, test certificates, and symbols	
Splash protection IPX4	•
c ETL US	•
Complies with Machinery Directive 2006/42/EC	•