

PW 6241 [EL]

Washing machine, electric heating

With individually programmable controls for the maximum in flexibility.



- Drum volume 8.48 (240) ft³ (l), load size 55 (24.5) lb (kg)
- Large program variety – application-specific wash programs
- Gentle laundry care thanks to the Miele honeycomb drum
- Particularly efficient – low water and energy consumption
- Perfect spinning results – residual moisture 43 %, g-factor 541

* Residual moisture specification relates to a hot rinse during the last rinse cycle.

EAN: 4002516584698 / Material number: 12092180 / Old Material Number: 51624167NAM

Construction type and design	
Design	Front loader
Product line	Professional
Front	Iron Grey
Control panel color	Stainless Steel
Load ratio	1:10
Load in lbs	55 (24.5)
Drum volume in cubic feet (l)	8.48 (240)
Door opening [Ø] in in.(mm)	16 15/16 (430)
Door opening angle in degrees	180
Door hinging	right
Maintenance-free motor with frequency converter	•
Honeycomb drum	•
Application	
Suitable for the hotel and catering industry	•
Suitable for senior living facilities	•
Suitable for facility management	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for fire brigades and rescue services	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centers	•
Performance data	
Tested virucidal efficacy	•
Proven hygiene	•
Specific water consumption for cold water connection in gal/lb	9.00
Specific energy consumption for cold water connection in kWh/lb	0.26
Specific water consumption for hot water connection in l/kg	8.80
Specific energy consumption for hot water connection in kWh/lb	0.10
Water consumption for cold water connection in l	216.0
Energy consumption for cold water connection in kWh	6.24
Energy consumption for cold water connection in Mops standard program in kWh	6.56
Program duration in minutes with cold water connection	60
Water consumption for hot water connection in l	211.0
Water consumption for hot water connection in Mops standard program in gal	276.1
Energy consumption for hot water connection in kW	2.40
Energy consumption for hot water connection in Mops standard program in kWh	1.66
Program duration in minutes with hot water connection	49
Water consumption in ECO program for cold water connection in l	212.3
Energy consumption in ECO program for cold water connection in kWh	5.04

PW 6241 [EL]

Washing machine, electric heating

With individually programmable controls for the maximum in flexibility.



EAN: 4002516584698 / Material number: 12092180 / Old Material Number: 51624167NAM

Program duration in minutes for ECO program with cold water connection	46
Water consumption in ECO program for hot water connection in l	212.5
Energy consumption in ECO program for hot water connection in kWh	1.44
Program duration in minutes for ECO program with hot water connection	36
Program runtime in minutes for Mops standard program with cold water connection	74
Program runtime in minutes for Mops standard program with hot water connection	57
Residual moisture with cold rinse in %	46
Residual moisture with hot rinse in %	43
Residual moisture when processing cleaning cloths in %	25
Spin speed in rpm	1100
g factor	541
Tested operating hours	30000
Control	
Control system	Profitronic M
Programmability	Freely programmable
Max. delay start in h	Can be selected freely
Countdown indicator	•
Program sequence indicator	•
Choice of display language	•
Standard/target group programs	
Basic programmes	•
Programmes for the hotel and catering industry	•
Programmes for retirement and care homes	•
Programmes for facility management	•
Programmes for dry cleaners	•
Programmes for small businesses	•
Programmes for fire brigades and rescue services	•
Programmes for studs, riding schools, and stables	•
Programmes for hospitals	•
Programmes for sports clubs	•
Programmes for beauty clinics, spas, and fitness studios	•
Dispensing	
Detergent dispenser drawer	3 compartments
Maximum number of connections for liquid dispenser pumps [number]	12
Empty sensor	•
Standard electrical connection	
Type of heating	Electric
Electrical connection	208/240 V 60 HZ 3 PH
Heater rating in kW	24.60
Total connected load in kW	26.20
Fuse rating in A	70
Water connection/drainage	
Cold water [number]	3 x 1/2" hose w/ 3/4" union
Hot water [number]	1x 1/2" hose w/ 3/4" th. union

PW 6241 [EL]

Washing machine, electric heating

With individually programmable controls for the maximum in flexibility.

EAN: 4002516584698 / Material number: 12092180 / Old Material Number: 51624167NAM

Dump valve	DN 70
Dimensions and weight	
External dimensions, net height in inches	64 13/16 (1646)
External dimensions, net width in inches	42 7/8 (1089)
External dimensions, net depth in inches	51 9/16 (1309)
External dimensions, gross height in inches	67 3/8 (1710)
External dimensions, gross width in inches	49 11/16 (1262)
External dimensions, gross depth in inches	58 (1472)
Net weight in lbs.(kg)	1517 (688.0)
Gross weight in lbs.	1630 (739)
Maximum floor load in N/m ²	9324
Emission values	
Emissions – sound pressure at workplace	73 dB(A) re 20 µPa
Heat dissipation into the room in BTU/h	4.70
Features	
Patented preliminary drainage	•
Patented cleaning cloth program	•
Imbalance monitoring	•
Temperature monitoring	•
Special heater element	•
Automatic load control Plus	•
Volumetric flow meter (optional)	•
Communication slot	•
Emergency shut off	•
Appliance-independent accessories	•
Efficiency and sustainability	
Recycling rate in %	96
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Serial interface module RS 232 (optional)	•
Peak-load negotiation/energy management (optional)	•
Logging operating data	•
Water recovery (optional)	•
Capacities	
Respirator masks [number]	20
Helmets [number]	6
Overalls [number]	4
Over jackets [number]	6
Chemical protection overalls [number]	2
Synthetic duvets [number]	2
Synthetic pillows [number]	4
Feather duvets [number]	2
Feather pillows [number]	4
Cloths, 22 g/0.8 oz[number]	578
Cotton mops, 40 cm/15.7 in[number]	126
Cotton mops, 50 cm/19.7 in[number]	112
Microfibre mops, 40 cm/15.7 in [number]]	223
Microfibre mops, 50 cm/19.7 in [number]	146
Mops, office, 100 g [quantity]	233
Mops, stairway, 150 g [quantity]	155

PW 6241 [EL]

Washing machine, electric heating

With individually programmable controls for the maximum in flexibility.



EAN: 4002516584698 / Material number: 12092180 / Old Material Number: 51624167NAM

Summer horse blankets [number]

4

Standards, test certificates, and symbols

Splash protection IPX4

•

c ETL US

•

Complies with Machinery Directive 2006/42/EC

•