

Complete C2 Hardfloor PowerLine - SFAE0

canister vacuum cleaners

with protective parquet floorhead for first-class care of delicate hard floors.



- Energy-efficient vacuuming – 1200 W
- AllTeQ floorhead is ideal for hard floors and low-pile carpet.
- Gentle on sensitive hard floors – soft parquet brush
- Adjustable working height – Stainless steel telescopic tube
- Effortless vacuuming of larger areas with 33 ft operating radius

EAN: 4002516612834 / Material number: 12157880 / Old Material Number: 41FAE036USA

Construction type	
Canister vacuum cleaner with dustbag	•
Product line	Complete C2
Motor type	PowerLine
Product type	SFAE0
Appliance color	Tech blue
Control panel	
Electronic suction power setting	6-stage rotary selector
Ergonomic carrying handle	•
Ergonomic handle	•
Silence system	•
Telescopic suction wand	Stainless steel telescopic tube
Park system for vacuuming breaks	•
Park system for storage	Both sides
Efficiency and sustainability	
Nominal power consumption in W	1100
Mobility	
Caster wheels gentle on floors	•
Three-point maneuverability	•
Operating radius in ft (m)	32 (10)
Cord length in ft (m)	21 (6.5)
Filter system	
FilterBag type	HyClean GN
FilterBag™ volume in qt (US) (l)	4.8 (4.5) qt (US) (l)
FilterBag™ change indicator	•
Exhaust filter	AirClean filter
Motor protection filter	•
Safety	
Locking system for floorhead and handle	•
Automatic FilterBag™ positioning	•
All-round bumper strip	•
Technical data	
Max. power in W	1200
Diameter in in. (mm)	19 1/4 (487)
Height in inch (mm)	227
Weight in lbs (kg)	20 (8.8)
Accessories supplied	
Three-piece accessory set	Integrated
Upholstery nozzle	•
Crevice nozzle	•
Dusting brush with synthetic bristles	•
Floorbrush	Parquet Twister XL SBB 400-3
SBD 365-3 floorhead	•
Parquet Twister XL Floorhead SBB 400-3	•
Filter	AirClean filter
Cleaning brush	No