

DOS G 80 comfort  
Hose metering pump  
with fill level indicator for automatic dispensing of liquid cleaning agents.

EAN: 4002516648000 / Material number: 12187400 / Old Material Number: 67747540NAM



- For canisters up to 12 13/16" (325 mm) tall (to canister opening)
- Dispensing up to 55 Milliliter per minute
- Adjustable via the dishwasher controls
- Flexible cap (covers DIN 50 and 51 threads)
- Min. canister opening: 1 1/4" (31 mm)

Machine affiliation	
PFD 401 U	•
PFD 404 U	•
PFD 408 U	•
Product category	
External dispenser system	•
Product characteristics	
Material	Plastic
Color	White
Production rate in ml/60 s	55
Length of suction wand in mm	13 7/8 (352)
Length of dispensing hose to suction wand in inches (mm)	1800
Length of dispensing hose from machine to dispenser module in inches (mm)	2850
Length of power cord to machine in inches (mm)	2800
Minimum width of canister opening in inches (mm)	31
Maximum width of canister opening in inches (mm)	60
Standard electrical connection	
Number of phases	1
Neutral conductor	N
AC/DC	AC
Voltage in V	200-240
Frequency in Hz	60
Total rated load in kW	0.01
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in inches	4 1/2 (114)
External dimensions, net width in inches	4 9/16 (115)
External dimensions, net depth in inches	5 1/2 (139)
External dimensions, gross height in inches	6 5/16 (160)
External dimensions, gross width in inches	7 13/16 (198)
External dimensions, gross depth in inches	18 7/8 (478)
Net weight in lbs	6 (2.32)
Gross weight in lbs	6 (2.60)