

## PDR 910 [G]

Professional vented dryer, gas heating  
with programmable M Touch Pro controls for the maximum in flexibility.



- Drum volume 6.36 (180.00) ft<sup>3</sup> (l), load size?? – ??
- Unique, gentle fabric care – patented honeycomb drum
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and WiFi
- Tested for intensive use – unique Miele quality

EAN: 4002516664772 / Material number: 12271750 /  
Old Material Number: 52910018NAM

<b>Construction type and design</b>	
Design	Front loader
Linie	Performance Plus
Front	Iron Grey
Control panel color	Stainless Steel
Load size with a load ratio of 1:20	20 (9.0) lb (kg)
Drum volume in ft <sup>3</sup> (l)	6.36 (180.00)
Drying system	Exhaust air
Door opening [Ø] in in.(mm)	17 3/8 (440)
Door opening angle in degrees	180
Door hinging	left
Stainless steel honeycomb drum	Yes
<b>Application</b>	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for fire brigades and rescue services	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas and fit ness centers	•
Suitable for doctors' and dentists' practices	•
Suitable for the petrochemical industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks and holiday complexes	•
Suitable for public/community care facilities	•
<b>Performance data</b>	
Specific energy consumption in kWh/kg an d kWh/p	0.52
Program cycle in min.	47
<b>Control</b>	
Control system	M Touch Pro
Programmability	programmable
Program controls	Residual moisture controlled
Max. delay start in h	24
Countdown indicator	•
Program sequence indicator	•
Choice of display language	•
<b>Standard electrical connection</b>	
Type of heating	Gas
Electrical connection	208/240 V 60 HZ 2 PH
Gas heater rating in kW	8.00
Total connected load in kW	0.32
Fuse rating in A	15

## PDR 910 [G]

Professional vented dryer, gas heating  
with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516664772 / Material number: 12271750 /  
Old Material Number: 52910018NAM

### Dimensions and weight of dryer

External dimensions, net height in inches	40 3/16 (1020)
External dimensions, net width in inches	27 9/16 (700)
External dimensions, net depth in inches	30 1/16 (763)
External dimensions, gross height in inches	47 7/8 (1215)
External dimensions, gross width in inches	29 15/16 (760)
External dimensions, gross depth in inches	32 5/16 (820)
Net weight in lbs. (kg)	159 (72.0)
Gross weight in lbs. (kg)	177 (80)
Maximum floor load in N	853

### Emission values

Emissions – sound pressure at workplace	50 dB(A) re 20 µPa
Heat output to the room in Mj/h and BTUs /h	3.90

### Features

Intelligent drum reversal	•
Axial airflow	•
Large-surface filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Communication slot	•
Drum lighting	•
Program selection via color frame	•
Machine-independent accessories	•

### Efficiency and sustainability

Recycling rate in %	89
---------------------	----

### Connection options

Payment system (optional)	•
Optical interface for service access	•
Peak-load negotiation / energy management (optional)	•
WiFi tumble dryer	•
Connector Box	•
LAN module (optional)	•

### Capacities

Respirator masks [number]	4
Standard and target group programs	1
Over jackets [number]	2
Synthetic duvets [number]	1
Synthetic pillows [number]	2
Feather duvets [number]	1
Feather pillows [number]	2
Cloths, 22 g/0.8 oz [number]	182
Cotton mops, 40 cm [number]	42
Cotton mops, 50 cm [number]	36
Microfibre mops, 40 cm [number]	66
Microfibre mops, 50 cm [number]	47
Summer horse blankets [number]	2

PDR 910 [G]

Professional vented dryer, gas heating  
with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516664772 / Material number: 12271750 /  
Old Material Number: 52910018NAM

Standards, test certificates, and symbols	
Splash-proof safety rating IPX4	•
c ETL US	•
Complies with Machinery Directive 2006/42/EC	•