

## EVS 7670

Handleless vacuum sealing drawer, 30" width and 9 3/16" height for professional vacuum sealing of food.

- Remaining fresh for longer – storage and portioning of food
- Intense taste sensations – food marination
- Preparation of food for sous-vide cooking
- Easy handling – Touch control and fully telescopic runners
- Push2open – opening the drawer couldn't be easier

EAN: 4002516764274 / Material number: 12423610 / Old Material Number: 30767051USA

<b>Construction type and design</b>	
Built-in vacuum drawer	•
VitroLine	•
ArtLine	•
No Handles	•
Color	Obsidian Black matte
<b>Convenience features</b>	
Preparing for Sous Vide cooking	•
Longer storage life of food	•
Marinating food	•
<b>Operating modes</b>	
Vacuumping	•
<b>Range of applications</b>	
Vacuum sealing food	•
Marinating food	•
Dividing food into portions	•
Vacuum sealing containers	•
Resealing original packaging	•
Sealing jars	•
Vacuum sealing liquids	•
<b>User convenience</b>	
Stainless-steel vacuum sealing chamber capacity in l	8.0
Storage compartment	•
Minimum bag size in inch (mm)	9 7/8 (250)
Maximum bag size in mm	13 7/8 (350)
Push2open mechanism	•
Fully telescopic runners for easy loading and unloading	•
Control panel with sensor control	•
Control panel with text	•
Timers	•
Stop programming	•
Timer function	•
LED vacuum setting indicator	•
LED vacuum strength indicator for external containers	•
Sealing duration settings	1 - 3
LED sealing duration indicator	•
Stop function	•
<b>Vacuum technology</b>	
Stainless-steel vacuum chamber	•
Pump capacity in m <sup>3</sup> /h	2.35 (4)
<b>Cleaning convenience</b>	
Flush control panel	•
Note regarding moisture removal from the vacuum pump	•
Replaceable sealing bar	•
<b>Safety</b>	
Safety cut-out	•
<b>Technical data</b>	
Appliance width in in. (mm)	29 7/8 (757)
Appliance height in in. (mm)	9 7/8 (248)
Appliance depth in in. (mm)	22 1/2 (570)

EVS 7670

Handleless vacuum sealing drawer, 30" width and 9 3/16" height  
for professional vacuum sealing of food.

EAN: 4002516764274 / Material number: 12423610 / Old Material Number: 30767051USA

Useable interior height in in. (mm)	3 1/4 (80)
Total connected load in kW	0.52
Voltage in V	120
Frequency in Hz	60
Fuse rating in A	10
Number of phases	1
Connection wire with plug	•
Wire length in ft. (m)	5 (1.8)
<b>Standard accessories</b>	
Adapter for vacuum-sealing container	1
Vacuum sealing bag support	1