

G 7193 SCVi AutoDos

Fully integrated ADA dishwasher

with Automatic Dispensing thanks to AutoDos with integrated PowerDisk.



- Wonderful use of space – the 3D MultiFlex tray with more room for your cutlery
- More information options and modern domestic appliance networking – Miele@home
- QuickIntenseWash, superior cleaning and drying in under 60 min
- Fresh water dishwashers – as little as ?? water consumed in Automatic program
- Very easy door opening and closing – ComfortClose

EAN: 4002516770688 / Material number: 12496700 / Old Material Number: 21719362USA

Type	
Fully integrated dishwashers	•
24 inch dishwasher	•
Design	
Fascia color	Stainless Steel.
Fascia panel version	Fully integrated fascia
Control type	Programme selector button
Control panel	1-line display with plain text
Display color	White
MultiLingua	•
Convenience	
Networking with Miele@home	•
Automatic dispensing with PowerDisk	•
Operating noise dB(A) re 1 pW	42
Countdown indicator	•
Delay start up to 24 hours	•
In-operation indication	optical and acoustic
Display language selection	•
Efficiency and sustainability	
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
Energy Star	•
Quality of results	
Fresh water dishwasher	•
AutoOpen drying	•
SensorDry	•
Active condensation drying	•
Perfect GlassCare	•
Wash programs	
ComfortWash	•
Pots & Pans	•
ComfortWash+	•
QuickIntenseWash	•
SaniWash	•
Extra Quiet 39 dB(A)	•
Appliance care	•
Rinse out salt	•
Rinse & Hold	•
Dishwashing options	
AutoDos	•
BottleClean	•
Quick	•
IntenseZone	•
Extra Clean	•
Extra dry	•
Baskets	
Cutlery loading	3D MultiFlex Tray
FlexCare glass holder	2

G 7193 SCVi AutoDos

Fully integrated ADA dishwasher

with Automatic Dispensing thanks to AutoDos with integrated PowerDisk.



EAN: 4002516770688 / Material number: 12496700 / Old Material Number: 21719362USA

FlexCare cup rack	2
Basket design	ExtraComfort
MultiClip	•
FlexCare Glass & Bottle	•
XL-Assist	•
Safety	
Waterproof system	•
Check filter saturation indicator	•
Technical data	
Niche width min in in.(mm)	23 5/8 (600)
Niche width max in in.(mm)	23 5/8 (600)
Niche height min in in.(mm)	32 1/8 (815)
Niche height max in in.(mm)	34 3/4 (880)
Niche depth in in.(mm)	21 3/4 (550)
Appliance width in in.(mm)	23 5/8 (598)
Appliance height in in.(mm)	32 1/8 (815)
Appliance depth in in.(mm)	21 3/4 (550)
Appliance depth with door open in in.(cm)	45 7/8 (116.5)
Net weight in lbs. (kg)	104 (47.0)
Total connected load in kW	1.40
Voltage in V	120
Fuse rating in A	15
Number of phases	1
Electrical frequency standard	60
Length of water inlet hose in ft (m)	5 (1.50)
Length of water drain hose in ft (m)	5 (1.50)
Length of electrical wire in ft (m)	4 (1.20)
Min. front panel weight in kg	4.0
Max. front panel weight in kg	11.0
[can be retrofitted by Service to min.]	7.0
[can be retrofitted by Service to max.]	14.0
Available display languages	
Available display languages via MultiLingua	deutsch, english (US), español, français (CA), português,
Standard accessories	
1 x PowerDisk	•
Voucher for 6 x PowerDisk	•

G 7193 SCVi AutoDos

Fully integrated ADA dishwasher

with Automatic Dispensing thanks to AutoDos with integrated PowerDisk.



G7000, fully integrated dishwasher, 60cm (installation drawing)

- 1) Plinth height 35-155 mm, 2) Plinth height 100-220 mm,
- 3) Appliance height max. 930 mm with plinth height conversion kit (Mat.-Nr. 6.394.761),