

G 7766 SCVi SF AutoDos

Fully-integrated, full-size dishwasher

with Automatic Dispensing thanks to AutoDos with integrated PowerDisk.



- Wonderful use of space – the 3D MultiFlex tray with more room for your cutlery
- More information options and modern domestic appliance networking – Miele@home
- QuickIntenseWash, superior cleaning and drying in under 60 min
- A perfect view for convenient loading even in the dark – BrilliantLight
- Clean Touch Steel front with handle in ContourLine design

EAN: 4002516770749 / Material number: 12496910 /
Old Material Number: 21776665USA

Type	
Fully integrated dishwashers	•
24 inch dishwasher	•
Design	
Fascia color	Obsidian Black
Fascia panel version	Fully integrated fascia
Control type	Softkeys
Control panel	1-line display with plain text
Display color	White
MultiLingua	•
Convenience	
Networking with Miele@home	•
Automatic dispensing with PowerDisk	•
Door closing aid	AutoClose
LED Lighting	•
Operating noise dB(A) re 1 pW	39
Countdown indicator	•
Delay start up to 24 hours	•
In-operation indication	Display, acoustic, volume control, optical
Display language selection	•
Efficiency and sustainability	
FlexiTimer	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
Quality of results	
Fresh water dishwasher	•
SensorDry	•
Active condensation drying	•
Perfect GlassCare	•
Wash programs	
QuickIntenseWash	•
Economy	•
Normal	•
ComfortWash	•
Pots & Pans	•
Automatic	•
IntenseWash	•
SaniWash	•
Energy Saver	•
Extra Quiet 37 dB(A)	•
Appliance care	•
Rinse out salt	•
Rinse & Hold	•
Filters	•

G 7766 SCVi SF AutoDos

Fully-integrated, full-size dishwasher

with Automatic Dispensing thanks to AutoDos with integrated PowerDisk.




EAN: 4002516770749 / Material number: 12496910 /
Old Material Number: 21776665USA

Dishwashing options	
AutoDos	•
BottleClean	•
Quick	•
IntenseZone	•
Extra Clean	•
Extra dry	•
Baskets	
Cutlery loading	3D MultiFlex Tray
FlexCare glass holder	2
FlexCare cup rack	1
Basket design	MaxiComfort
MultiClip	•
FlexCare Glass & Bottle	•
XL-Assist	•
StrawClean	•
Safety	
Waterproof system	•
Check filter saturation indicator	•
Technical data	
Niche width min in in.(mm)	23 5/8 (600)
Niche width max in in.(mm)	23 5/8 (600)
Niche height min in in.(mm)	33 3/4 (855)
Niche height max in in.(mm)	36 1/4 (920)
Niche depth in in.(mm)	22 1/2 (570)
Appliance width in in.(mm)	23 5/8 (598)
Appliance height in in.(mm)	33 3/4 (855)
Appliance depth in in.(mm)	22 1/2 (570)
Appliance depth with door open in in.(cm)	47 1/2 (120.5)
Net weight in lbs. (kg)	120 (54.0)
Total connected load in kW	1.40
Voltage in V	120
Fuse rating in A	15
Number of phases	1
Electrical frequency standard	60
Length of water inlet hose in ft (m)	5 (1.50)
Length of water drain hose in ft (m)	5 (1.50)
Length of electrical wire in ft (m)	4 (1.20)
Min. front panel weight in kg	4.0
Max. front panel weight in kg	12.0
Replacing bulbs	Customer Service
Available display languages	
Available display languages via MultiLingua	deutsch, english (US), español, français (CA), português, [?][?][?][?]
Standard accessories	
1 x PowerDisk	•
Voucher for 6 x PowerDisk	•

G 7766 SCVi SF AutoDos

Fully-integrated, full-size dishwasher

with Automatic Dispensing thanks to AutoDos with integrated PowerDisk.



G7000/5000 SF, fully integrated dishwasher, 60cm
(installation drawing)

1) Plinth height 35-155 mm, 2) Plinth height 100-220 mm, 3) Appliance height max. 970 mm with plinth height conversion kit (Mat.-Nr. 6.394.761),