

G 7791 SCVi AutoDos K2O

Fully integrated ADA dishwasher

with Automatic Dispensing thanks to AutoDos with integrated PowerDisk.



- Wonderful use of space – the 3D MultiFlex tray with more room for your cutlery
- More information options and modern domestic appliance networking – Miele@home
- Combining perfection in kitchen design with automatic opening – Knock2open
- A perfect view for convenient loading even in the dark – BrilliantLight
- Maximum flexibility and premium basket design – MaxiComfort baskets

EAN: 4002516770756 / Material number: 12496920 /
Old Material Number: 21779162USA

Type	
Fully integrated dishwashers	•
24 inch dishwasher	•
Design	
Fascia color	Obsidian Black
Fascia panel version	Fully integrated fascia
Control type	Softkeys
Control panel	1-line display with plain text
Display color	White
MultiLingua	•
Convenience	
Networking with Miele@home	•
Automatic dispensing with PowerDisk	•
Knock2open	•
LED Lighting	•
Operating noise dB(A) re 1 pW	39
Countdown indicator	•
Delay start up to 24 hours	•
In-operation indication	optical and acoustic, volume control
Display language selection	•
Efficiency and sustainability	
FlexiTimer	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
Quality of results	
Fresh water dishwasher	•
SensorDry	•
Active condensation drying	•
Perfect GlassCare	•
Wash programs	
QuickIntenseWash	•
Economy	•
Normal	•
ComfortWash	•
Pots & Pans	•
China & Crystal	•
SaniWash	•
Energy Saver	•
Extra Quiet 37 dB(A)	•
Appliance care	•
Rinse out salt	•
Filters	•
Dishwashing options	
AutoDos	•
BottleClean	•

G 7791 SCVi AutoDos K2O

Fully integrated ADA dishwasher

with Automatic Dispensing thanks to AutoDos with integrated PowerDisk.



EAN: 4002516770756 / Material number: 12496920 /
Old Material Number: 21779162USA

Quick	•
IntenseZone	•
Extra Clean	•
Extra dry	•
Baskets	
Cutlery loading	3D MultiFlex Tray
FlexCare glass holder	2
FlexCare cup rack	1
Basket design	MaxiComfort
MultiClip	•
FlexCare Glass & Bottle	•
XL-Assist	•
StrawClean	•
Safety	
Waterproof system	•
Check filter saturation indicator	•
Technical data	
Niche width min in in.(mm)	23 5/8 (600)
Niche width max in in.(mm)	23 5/8 (600)
Niche height min in in.(mm)	32 1/8 (815)
Niche height max in in.(mm)	34 3/4 (880)
Niche depth in in.(mm)	21 3/4 (550)
Appliance width in in.(mm)	23 5/8 (598)
Appliance height in in.(mm)	32 1/8 (815)
Appliance depth in in.(mm)	21 3/4 (550)
Appliance depth with door open in in.(cm)	45 7/8 (116.5)
Net weight in lbs. (kg)	106 (48.0)
Total connected load in kW	1.40
Voltage in V	120
Fuse rating in A	15
Number of phases	1
Electrical frequency standard	60
Length of water inlet hose in ft (m)	5 (1.50)
Length of water drain hose in ft (m)	5 (1.50)
Length of electrical wire in ft (m)	4 (1.20)
Min. front panel weight in kg	4.0
Max. front panel weight in kg	11.0
[can be retrofitted by Service to min.]	7.0
[can be retrofitted by Service to max.]	14.0
Replacing bulbs	Customer Service
Available display languages	
Available display languages via MultiLingua	deutsch, english (US), español, français (CA), português, [?] [?] [?] [?]
Standard accessories	
1 x PowerDisk	•
Voucher for 6 x PowerDisk	•