

G 7936 SCi AutoDos  
Semi-integrated dishwasher  
- the Miele all-rounder for highest demands.



- Convenient, efficient, sustainable – perfect results with automatic dispensing
- Wonderful use of space – the 3D MultiFlex tray with more room for your cutlery
- More information options and modern domestic appliance networking – Miele@home
- A perfect view for convenient loading even in the dark – BrilliantLight
- Intuitive, fast, and clear touch operation – M Touch display

EAN: 4002516770770 / Material number: 12496970 /  
Old Material Number: 21793654USA

<b>Type</b>	
Semi-integrated dishwashers	•
24 inch dishwasher	•
<b>Design</b>	
Fascia color	Obsidian Black
Fascia panel version	Slanted fascia
Control type	Touch control
Control panel	M Touch S Display
Display color	White
MultiLingua	•
<b>Convenience</b>	
Networking with Miele@home	•
Automatic dispensing with PowerDisk	•
Door closing aid	AutoClose
LED Lighting	•
Operating noise dB(A) re 1 pW	39
Countdown indicator	•
Delay start up to 24 hours	•
In-operation indication	Display, acoustic, volume control
Display language selection	•
<b>Efficiency and sustainability</b>	
FlexiTimer	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
<b>Quality of results</b>	
Fresh water dishwasher	•
SensorDry	•
Active condensation drying	•
Perfect GlassCare	•
<b>Wash programs</b>	
QuickIntenseWash	•
Economy	•
Normal	•
ComfortWash	•
Pots & Pans	•
Automatic	•
IntenseWash	•
SaniWash	•
Energy Saver	•
Extra Quiet 37 dB(A)	•
Tall items	•
Glasses – No Rinse Aid	•
Appliance care	•
Rinse out salt	•
Rinse & Hold	•

G 7936 SCi AutoDos  
Semi-integrated dishwasher  
- the Miele all-rounder for highest demands.



EAN: 4002516770770 / Material number: 12496970 /  
Old Material Number: 21793654USA

Filters	•
<b>Dishwashing options</b>	
AutoDos	•
BottleClean	•
Quick	•
IntenseZone	•
Extra Clean	•
Extra dry	•
<b>Baskets</b>	
Cutlery loading	3D MultiFlex Tray
FlexCare glass holder	2
FlexCare cup rack	1
Basket design	MaxiComfort
MultiClip	•
FlexCare Glass & Bottle	•
XL-Assist	•
StrawClean	•
<b>Safety</b>	
Waterproof system	•
Check filter saturation indicator	•
Child Safety lock	•
System lock	•
<b>Technical data</b>	
Niche width min in in.(mm)	23 5/8 (600)
Niche width max in in.(mm)	23 5/8 (600)
Niche height min in in.(mm)	33 3/4 (855)
Niche height max in in.(mm)	36 1/4 (920)
Niche depth in in.(mm)	22 1/2 (570)
Appliance width in in.(mm)	23 5/8 (598)
Appliance height in in.(mm)	33 3/4 (855)
Appliance depth in in.(mm)	22 1/2 (570)
Appliance depth with door open in in.(cm)	47 1/2 (120.5)
Net weight in lbs. (kg)	109 (49.2)
Total connected load in kW	1.40
Voltage in V	120
Fuse rating in A	15
Number of phases	1
Electrical frequency standard	60
Length of water inlet hose in ft (m)	5 (1.50)
Length of water drain hose in ft (m)	5 (1.50)
Length of electrical wire in ft (m)	4 (1.20)
Min. front panel weight in kg	3.0
Max. front panel weight in kg	10.0
[can be retrofitted by Service to min.]	5.0
[can be retrofitted by Service to max.]	14.0
Replacing bulbs	Customer Service

G 7936 SCi AutoDos  
Semi-integrated dishwasher  
- the Miele all-rounder for highest demands.



EAN: 4002516770770 / Material number: 12496970 /  
Old Material Number: 21793654USA

#### Available display languages

Available display languages via MultiLingua

bahasa malaysia, dansk,  
deutsch, english (AU),  
english (GB), english (US),  
español, français (FR),  
hrvatski, italiano, magyar,  
nederlands, norsk, polski,  
português, русский,  
română, slovenčina,  
slovenščina, srpski, suomi,  
svenska, türkçe, українська,  
čeština, ελληνικά,  
□□□□□□□□, □□, □  
□□, □□□□, □□□

#### Standard accessories


1 x PowerDisk

•

Voucher for 6 x PowerDisk

•

G 7936 SCi AutoDos  
Semi-integrated dishwasher  
- the Miele all-rounder for highest demands.



G7000, integrated dishwasher, XXL, 60cm (installation drawing)

1) Plinth height 35-155 mm, 2) Plinth height 100-220 mm, 3) Appliance height max. 970 mm with plinth height conversion kit (Mat.-Nr. 6.394.761), ,