

G 7986 SCVi AutoDos K2O

Fully-integrated, full-size dishwasher

- the Miele all-rounder for highest demands.



- Convenient, efficient, sustainable – perfect results with automatic dispensing
- Wonderful use of space – the 3D MultiFlex tray with more room for your cutlery
- More information options and modern domestic appliance networking – Miele@home
- A perfect view for convenient loading even in the dark – BrilliantLight
- Intuitive, fast, and clear touch operation – M Touch display

EAN: 4002516770787 / Material number: 12496980 /
Old Material Number: 21798662USA

Type	
Fully integrated dishwashers	•
24 inch dishwasher	•
Design	
Fascia color	Clean Touch Steel/Obsidian Black
Fascia panel version	Fully integrated fascia
Control type	Touch control
Control panel	M Touch Vi
Display color	White
MultiLingua	•
Convenience	
Networking with Miele@home	•
Automatic dispensing with PowerDisk	•
Knock2open	•
Door closing aid	AutoClose
LED Lighting	•
Operating noise dB(A) re 1 pW	39
Countdown indicator	•
Delay start up to 24 hours	•
In-operation indication	Display, acoustic, volume control, optical
Display language selection	•
Efficiency and sustainability	
FlexiTimer	•
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
Quality of results	
Fresh water dishwasher	•
SensorDry	•
Active condensation drying	•
Perfect GlassCare	•
Wash programs	
QuickIntenseWash	•
Economy	•
Normal	•
ComfortWash	•
Pots & Pans	•
Automatic	•
IntenseWash	•
SaniWash	•
Energy Saver	•
Extra Quiet 37 dB(A)	•
Tall items	•
Glasses – No Rinse Aid	•
Appliance care	•

G 7986 SCVi AutoDos K2O

Fully-integrated, full-size dishwasher

- the Miele all-rounder for highest demands.



EAN: 4002516770787 / Material number: 12496980 /
Old Material Number: 21798662USA

Rinse out salt	•
Rinse & Hold	•
Filters	•
Dishwashing options	
AutoDos	•
BottleClean	•
Quick	•
IntenseZone	•
Extra Clean	•
Extra dry	•
Baskets	
Cutlery loading	3D MultiFlex Tray
FlexCare glass holder	2
FlexCare cup rack	1
Basket design	MaxiComfort
MultiClip	•
FlexCare Glass & Bottle	•
XL-Assist	•
StrawClean	•
Safety	
Waterproof system	•
Check filter saturation indicator	•
Technical data	
Niche width min in in.(mm)	23 5/8 (600)
Niche width max in in.(mm)	23 5/8 (600)
Niche height min in in.(mm)	33 3/4 (855)
Niche height max in in.(mm)	36 1/4 (920)
Niche depth in in.(mm)	21 3/4 (550)
Appliance width in in.(mm)	23 5/8 (598)
Appliance height in in.(mm)	33 3/4 (855)
Appliance depth in in.(mm)	21 3/4 (550)
Appliance depth with door open in in.(cm)	47 1/2 (120.5)
Net weight in lbs. (kg)	109 (49.0)
Total connected load in kW	1.40
Voltage in V	120
Fuse rating in A	15
Number of phases	1
Electrical frequency standard	60
Length of water inlet hose in ft (m)	5 (1.50)
Length of water drain hose in ft (m)	5 (1.50)
Length of electrical wire in ft (m)	4 (1.20)
Min. front panel weight in kg	4.0
Max. front panel weight in kg	12.0
Replacing bulbs	Customer Service


G 7986 SCVi AutoDos K2O
 Fully-integrated, full-size dishwasher
 - the Miele all-rounder for highest demands.



EAN: 4002516770787 / Material number: 12496980 /
 Old Material Number: 21798662USA

Available display languages	
Available display languages via MultiLingua	bahasa malaysia, dansk, deutsch, english (AU), english (GB), english (US), español, français (FR), hrvatski, italiano, magyar, nederlands, norsk, polski, portuguis, русский, română, slovenčina, slovenščina, srpski, suomi, svenska, türkçe, українська, čeština, ελληνικά, [?][?][?][?][?][?][?], [?][?], [?] [?][?], [?][?][?][?], [?][?][?]
Standard accessories	
1 x PowerDisk	•
Voucher for 6 x PowerDisk	•

G 7986 SCVi AutoDos K2O
Fully-integrated, full-size dishwasher
- the Miele all-rounder for highest demands.



G7000, fully integrated dishwasher, XXL, 60cm
(installation drawing)

1) Plinth height 35-155 mm, 2) Plinth height 100-220 mm, 3) Appliance height max. 970 mm with plinth height conversion kit (Mat.-Nr. 6.394.761),