

## G 7266 SCVi SF

Fully-integrated, full-size dishwasher  
with 3D MultiFlex Tray for maximum convenience.



- QuickIntenseWash, superior cleaning and drying in under 60 min
- Completely dry – Miele AutoOpen drying
- Very easy door opening and closing – ComfortClose
- Clean Touch Steel front with handle in ContourLine design

EAN: 4002516770824 / Material number: 12497150 /  
Old Material Number: 21726665USA

<b>Available display languages</b>	
Available display languages via MultiLingua	deutsch, english (US), español, français, português, [?][?][?][?]
<b>Type</b>	
Fully integrated dishwashers	•
24 inch dishwasher	•
<b>Design</b>	
Fascia color	Stainless Steel.
Fascia panel version	Fully integrated fascia
Control type	Programme selector buttons
Control panel	1-line display with plain text
Display color	White
MultiLingua	•
<b>Convenience</b>	
Networking with Miele@home	•
Door closing aid	AutoClose
Operating noise dB(A) re 1 pW	42
Countdown indicator	•
Delay start up to 24 hours	•
In-operation indication	optical and acoustic
Display language selection	•
<b>Efficiency and sustainability</b>	
EcoPower Technology	•
Proven hygiene	•
Hot water connection	•
Half load	•
Energy Star	•
<b>Quality of results</b>	
Fresh water dishwasher	•
AutoOpen drying	•
SensorDry	•
Active condensation drying	•
Perfect GlassCare	•
<b>Wash programs</b>	
QuickIntenseWash	•
ComfortWash	•
Pots & Pans	•
SaniWash	•
Extra Quiet 39 dB(A)	•
Appliance care	•
Rinse out salt	•
Rinse & Hold	•
<b>Dishwashing options</b>	
BottleClean	•
Quick	•
IntenseZone	•

## G 7266 SCVi SF

Fully-integrated, full-size dishwasher  
with 3D MultiFlex Tray for maximum convenience.




EAN: 4002516770824 / Material number: 12497150 /  
Old Material Number: 21726665USA

Extra Clean	•
Extra dry	•
<b>Baskets</b>	
Cutlery loading	3D MultiFlex Tray
FlexCare glass holder	2
FlexCare cup rack	1
Basket design	ExtraComfort
MultiClip	•
FlexCare Glass & Bottle	•
XL-Assist	•
<b>Safety</b>	
Waterproof system	•
Check filter saturation indicator	•
<b>Technical data</b>	
Niche width min in in.(mm)	23 5/8 (600)
Niche width max in in.(mm)	23 5/8 (600)
Niche height min in in.(mm)	33 3/4 (855)
Niche height max in in.(mm)	36 1/4 (920)
Niche depth in in.(mm)	22 1/2 (570)
Appliance width in in.(mm)	23 5/8 (598)
Appliance height in in.(mm)	33 3/4 (855)
Appliance depth in in.(mm)	22 1/2 (570)
Appliance depth with door open in in.(cm)	47 1/2 (120.5)
Net weight in lbs. (kg)	120 (54.0)
Total connected load in kW	1.40
Voltage in V	120
Fuse rating in A	15
Number of phases	1
Electrical frequency standard	60
Length of water inlet hose in ft (m)	5 (1.50)
Length of water drain hose in ft (m)	5 (1.50)
Length of electrical wire in ft (m)	4 (1.20)
Min. front panel weight in kg	4.0
Max. front panel weight in kg	10.0
[can be retrofitted by Service to min.]	7.0
[can be retrofitted by Service to max.]	14.0
<b>Standard accessories</b>	
1 x UltraTabs box (20 tabs)	•
Voucher for 1 x box of UltraTabs (20 tabs) or 3 boxes (60 tabs in each) at a reduced price	•

## G 7266 SCVi SF

Fully-integrated, full-size dishwasher  
with 3D MultiFlex Tray for maximum convenience.



G7000/5000 SF, fully integrated dishwasher, 60cm  
(installation drawing)

1) Plinth height 35-155 mm, 2) Plinth height 100-  
220 mm, 3) Appliance height max. 970 mm with plinth  
height conversion kit (Mat.-Nr. 6.394.761),