

DAC 2247 Stella  
Ceiling extractor  
in compact design in 45 7/8 (1165) in (mm) width



- Suitable for every home – vented or recirculating
- Convenient operation – with Con@ctivity and remote control included
- Powerful – ?? in Booster level
- Efficient filtration- 10-ply stainless steel grease filters
- Panel

EAN: 4002516805946 / Material number: 12565890 /  
Old Material Number: 28C2247SUSA

<b>Construction type and design</b>	
Appliance colour	Stainless steel
<b>Design</b>	
Ceiling fan	•
<b>Operating modes</b>	
Recirculated mode	Can be retrofitted
OdorFree charcoal filter (order separately)	DKF 35-P
<b>Design</b>	
Edge extraction	•
<b>User convenience</b>	
Miele@home	•
Automatic function Con@ctivity	•
Electronic controls	•
EasySwitch	•
ON/OFF switch	•
Power levels (number excl. Intensive)	3
Booster levels	1
Programmable Intensive switch-off	•
Delayed shutdown for 5 or 15 minutes	•
Grease filter saturation indicator	•
Active charcoal filter saturation indicator	•
<b>Efficiency and sustainability</b>	
ECO motor	•
PowerManagement system	•
<b>Cleaning convenience</b>	
Easy-to-clean canopy interior – CleanCover	•
<b>Filter system</b>	
Number of dishwasher-safe stainless steel grease filters (10-ply)	4
<b>Lighting</b>	
LED	•
Number x W	2 x 7,2 W
Light intensity in lx	450 lx
Color temperature in K	3500 Kelvin
<b>Blower</b>	
Dual-action blower	•
DC motor	•
<b>Exhaust air</b>	
Maximum air throughput in cfm according to HVI	356
Air throughput	Values upon request
<b>Safety</b>	
Safety shut-off	•
<b>Technical data</b>	
Overall min. height for vented and external in in. (mm)	11 3/4 (296)
Canopy width in in.(mm)	45 7/8 (1165)
Overall max. height for vented and external in in. (mm)	11 3/4 (296)
Canopy height in in.(mm)	11 3/4 (296)
Overall min. height for recirculation in in. (mm)	11 3/4 (296)


DAC 2247 Stella  
Ceiling extractor  
in compact design in 45 7/8 (1165) in (mm) width



EAN: 4002516805946 / Material number: 12565890 /  
Old Material Number: 28C2247SUSA

Canopy depth in in.(mm)	19 3/4 (500)
Overall max. height for recirculation in in. (mm)	11 3/4 (296)
Net weight in lbs. (kg)	50 (22.3)
Length of electrical wire in ft (m)	2 (0.7)
Standard plug fitted	•
Minimum height above electric cooktops in mm	24 1/8 (610)
Minimum safety distance above gas cooktops (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	26 (660)
Number of phases	1
Total connected load in kW	0.19
Voltage in V	120
Fuse rating in A	15
Frequency in Hz	60
<b>Installation note</b>	
Vent connection on side	•
Diameter of vent connection in in.(mm)	6 (150)
<b>Standard accessories</b>	
Reducer from 150 to 125 mm Ø	•
Remote control	•
Non-return flap	•

DAC 2247 Stella  
Ceiling extractor  
in compact design in 45 7/8 (1165) in (mm) width



DAC2247, Installation drawings

A) Exhaust air mode, B) Recirculation mode with integrated odour filter, 1) Exhaust air connection  $\varnothing$  150 mm, The connection piece is on the left-hand side ex works., -The housing can be rotated by 90 degrees for exhaust air routing to the front or rear. To allow the housing to be rotated, there must be a free space of 100 mm in the ceiling in front of and behind the ceiling cut-out., -For an exhaust air duct to the right, the extractor bonnet must be installed rotated by 180 degrees., 2) Spigot  $\varnothing$  150 mm as air outlet in Plug&Play mode or for connecting an air duct in ducted recirculation mode. The connection piece is on the left-hand side ex works., -It is not possible to convert the spigot to the front or rear., -For an exhaust air duct to the right, the cooker bonnet must be installed rotated by 180 degrees.