

## Duoflex HX1 Extra

Cordless stick vacuum cleaner

powerful | Grab&Go | light and compact | attachment for sensitive surfaces



- Lithium-ion battery: Up to 55 minutes runtime with a single charge<sup>\*</sup>
- Modern design: Brilliant White w/ applications in space gray + high-quality feel
- 99.99%<sup>\*\*</sup> dust retention capacity with Hygiene filter
- Incl. flexible universal brush for cleaning sensitive surfaces
- Intelligent electrobrush with automatic power adjustment
- Light and compact: 3.1 kg/0.3 L dust container
- Convenient Grab&Go function thanks to the SpeedLock system wall bracket
- As powerful as a conventional Miele vacuum cleaner<sup>\*\*\*</sup>

<sup>\*</sup> Valid for power level 1 without connected electrobrush.

<sup>\*\*</sup> In accordance with IEC 62885-4

<sup>\*\*\*</sup> Cleaning performance compared with a Miele Complete C3 canister vacuum cleaner (SGEF3) with STB 305-3 turbobrush (dust pickup from carpet and hard floor with crevices, fiber pickup from carpet). In accordance with IEC 62885-2.

EAN: 4002516800828 / Material number: 12580550 / Old Material Number: 41QLL035USA

<b>Design</b>	
Cordless stick vacuum cleaner	•
Product line	Duoflex HX1
Motor type	Digital Efficiency Motor
Product type	SQLL0
<b>Construction type and design</b>	
Color	Brilliant white
<b>Cleaning</b>	
Vortex Technology	•
<b>User convenience</b>	
Electronic suction power setting	Buttons/2 levels
Wall bracket	Speedlock
SpeedLock system	SpeedLock system
Accessory storage	HX-AH 20
<b>Filter system</b>	
ComfortClean	•
Dustbag volume in cu. ft. (l)	0.01 (0.3)
<b>Technical data</b>	
Battery type	Li-ion
Nominal battery capacity in mAh	2500
Volume in dB	79.0
Width in inches (mm)	10 1/4 (260)
Height in inch (mm)	1250
Weight in lbs (kg)	7 (3.1)
Running time MIN-stage PowerUnit solo	55
Cleaning area in m <sup>2</sup>	60
Recharging time in min.	210
Power rating in W	160
<b>Standard accessories</b>	
Cleaning brush	Integrated
MultiFloor electrobrush HX-EB 20	•
HX-DB dust brush	•
HX-UN upholstery nozzle	•
HX-CN crevice nozzle	•