

APLW 905

Built-in report printer

retrofitting kit for printing process protocols.



- Thermal printer with 2 3/8" (60 mm) paper width
- Installed by Miele Service

EAN: 4002516915027 / Material number: 12685170 / Old Material Number: 69242019D

Product category	
SlimLine laboratory glasswashers	•
Machine affiliation	
PLW 7111	•
PLW 7111 [Safety]	•
PWD 7121	•
PWD 7122	•
Product category	
Conversion kit	•
Process documentation/operating documentation/communication	•
Application area	
Routine monitoring of the cleaning and disinfection process	•
Product characteristics	
Material	Plastic
Color	Black
Dimensions and weight	
External dimensions, gross height in inches	5 15/16 (150)
External dimensions, gross width in inches	13 7/16 (340)
External dimensions, gross depth in inches	29 9/16 (750)
Net weight in lbs	6 (2.51)
Gross weight in lbs	8 (3.44)