

Guard M1 Parquet XL canister vacuum cleaners powerful suction | stylish design | ideal for large hard floors



- ComfortFit: developed for the highest hygiene standards
- Durable: tested for the equivalent of 20 years** use
- Height-adjustable EasySlide telescopic tube
- Parquet Twister brush for gentle cleaning of hard floors
- Ideal for places that are hard to reach: flexible crevice nozzle
- Parquet Twister XL (41 cm): ideal for large hard floors
- AirClean Plus: more than 99.99%** dust retention capacity
- Mode button: Easily adapt the suction power to suit your needs
- Practical compartment with three-piece accessory set for added convenience
- Stylish design concept and illuminated LED icons
- Extra range, fewer socket changes: 11 m operating radius

* During the development phase of the advertised Guard vacuum cleaner series, Miele tested models and core components at various power levels for 750 hours of use (= 37.5 hours p.a.). More:

mieleusa.com/20years

** In accordance with IEC 62885-2:2021

EAN: 4002516856009 / Material number: 12704680 /
Old Material Number: 41VTE037CDN

Design	
Canister vacuum cleaner with dustbag	•
Product line	Guard M1
Motor type	PowerLine
Product type	SVTE0
Construction type and design	
Appliance color	Brilliant white
User convenience	
Electronic suction power setting	MODE button
Ergonomic carrying handle	•
Ergonomic handle	•
Telescopic suction wand	HES mid-size telescopic wand
Park system for vacuuming breaks	•
One-touch automatic cord rewind	•
Mobility	
Caster wheels gentle on floors	•
Three-point maneuverability	•
Operating radius in ft (m)	36 (11)
Cord length in ft (m)	24 (7.5)
Filter system	
FilterBag type	HyClean Pure CO
FilterBag™ volume in qt (US) (l)	4.8 (4.5) qt (US) (l)
FilterBag™ change indicator	•
Exhaust filter	AirClean Plus filter
Motor protection filter	•
Safety	
Locking system for floorhead and handle	•
Automatic FilterBag™ positioning	•
All-round bumper strip	•
Technical data	
Power	1200
Volume in dB	74.0
Width in inches (mm)	19 5/8 (496)
Height in inch (mm)	227
Depth in mm	28.40
Weight in lbs (kg)	15 (6.7)
Standard accessories	
Three-piece accessory set	Integrated
Upholstery nozzle	•
Crevice nozzle	•
Dust brush	•
Floorhead SBD 365-3	•
HyClean Air CO vacuum bag	•