

## Guard S1

canister vacuum cleaners

high suction power | light, compact | in modern trend colors | height-adjustable



- ComfortFit: developed for the highest hygiene standards
- Ergonomic handle: for comfortable handling
- 99.99%\* dust retention capacity with AirClean filter
- Durable: tested for the equivalent of 20 years\*\*\* use
- 10 m operating radius: effortless cleaning of larger areas
- Effortless handling thanks to light and compact design
- Height-adjustable EasySlide telescopic tube

\* In accordance with IEC 62885-2:2021

\*\* During the development phase of the advertised Guard vacuum cleaner series, Miele tested models and core components at various power levels for 750 hours of use (= 37.5 hours p.a.). More:

[mieleusa.com/20years](http://mieleusa.com/20years)

EAN: 4002516867272 / Material number: 12752460 /  
Old Material Number: 41TAE032CDN

| General information                     |                           |
|-----------------------------------------|---------------------------|
| Model number                            | Guard S1                  |
| Manufacturer material number            | 12752460                  |
| EAN number                              | 4002516867272             |
| Design                                  |                           |
| Canister vacuum cleaner with dustbag    | •                         |
| Product line                            | Guard S1                  |
| Motor type                              | PowerLine                 |
| Product type                            | STAE0                     |
| Construction type and design            |                           |
| Color                                   | Nordic blue               |
| User convenience                        |                           |
| Electronic suction power setting        | 4-stage rotary selector   |
| Comfort handle                          | •                         |
| Comfort handle with integrated controls | •                         |
| Telescopic suction wand                 | EasySlide telescopic wand |
| Park system for vacuuming breaks        | •                         |
| Mobility                                |                           |
| Caster wheels gentle on floors          | •                         |
| Three-point maneuverability             | •                         |
| Operating radius in ft (m)              | 32 (10)                   |
| Cord length in ft (m)                   | 21 (6.5)                  |
| Filter system                           |                           |
| FilterBag type                          | HyClean Pure TU           |
| FilterBag™ volume in qt (US) (l)        | 3.7 (3.5) qt (US) (l)     |
| FilterBag™ change indicator             | •                         |
| Exhaust filter                          | AirClean filter           |
| Motor protection filter                 | •                         |
| Safety                                  |                           |
| Locking system for floorhead and handle | •                         |
| Automatic FilterBag™ positioning        | •                         |
| Furniture protection                    | •                         |
| Technical data                          |                           |
| Power                                   | 1200                      |
| Volume in dB                            | 78.0                      |
| Width in inches (mm)                    | 16 3/4 (425)              |
| Height in inches (mm)                   | 9 (230)                   |
| Depth in inches (mm)                    | 9 5/8 (245)               |
| Weight in lbs (kg)                      | 14 (6.0)                  |
| Standard accessories                    |                           |
| Upholstery nozzle                       | •                         |
| Crevice nozzle                          | •                         |
| Dust brush                              | •                         |
| Floorhead SBD 355-3                     | •                         |
| HyClean Air TU vacuum bag               | •                         |