

TXF360WP

T1 Heat-Pump Dryer:

18 lb | DirectSensor | Honeycomb drum | FragranceDos | Miele@home | EcoDry



- Heat pump technology – low consumption, gentle drying
- PerfectDry ensures that your laundry is not too damp or too dry
- FragranceDos2 ensures your laundry smells wonderfully fresh after drying*
- -
- Easy fingertip operation – DirectSensor

* Patent EP 2 431 516

EAN: 4002516944737 / Material number: 12819080 /

Old Material Number: 12XF3602NAM

General information	
Model number	TXF360WP
Manufacturer material number	12819080
EAN number	4002516944737
Marketing class	Gold
Design	
Stackable	•
Door hinging	right, Reversible
Side-by-Side	•
Slot-in	•
Type	
Product brand	T1 White Edition
Heat-pump dryer	•
Design	
Appliance color	Lotus white
Control panel color	Lotus white
Door design	Obsidian Black with white ring
Rotary selector color	Lotus white
Fascia panel version	5° inclined
Control type	Selector dial
Display	DirectSensor white, 7-segment
Drying results	
PerfectDry precision drying	•
FragranceDos ² fragrance system	•
Intelligent drum reversal	•
Gentle laundry care	
Honeycomb drum	•
Load in lbs. (kg)	18 (8)
User convenience	
Networking with Miele@home	•
Wash2Dry	•
Delay start up to 24 hours	•
Countdown indicator	•
Drum lighting	LED
Condensed water container	•
Integrated condensed water drainage	•
AddLoad	•
Smart Extras	
Wash2Dry	•
Push notifications	•
MobileStart	•
Alexa voice control	•
Google voice control	•
AI Diagnostics	•
RemoteUpdate	•
Smart Home Integration	•

TXF360WP

T1 Heat-Pump Dryer:

18 lb | DirectSensor | Honeycomb drum | FragranceDos | Miele@home | EcoDry



EAN: 4002516944737 / Material number: 12819080 /
Old Material Number: 12XF3602NAM

Efficiency	
DryProtect	•
Maintenance-free heat exchanger	•
DuraLife motor	•
Drying programs	
Delicates	•
Woollens	•
Express	•
Denim	•
Outerwear	•
Proofing	•
Warm air/DryFresh	•
Normal	•
Dress Shirts	•
Bed Linens	•
Drying extras	
Anti-crease action	•
Gentle tumble	•
Acoustic signal	•
Quality	
Soft ribs	•
Safety	
Lock code	•
Empty out container" indicator	•
Clean filter" indication	•
Optical interface	•
Technical data	
Dimensions (H x W x D) in inches (mm)	33 1/2 (850) x 23 1/2 (596) x 25 3/8 (643)
Dimensions (width) in in. (mm)	23 1/2 (596)
Dimensions (height) in in. (mm)	33 1/2 (850)
Dimensions (depth) in in. (mm)	25 3/8 (643)
Weight in lbs. (kg)	135 (61)
Voltage in V	120
Fuse rating in A	15
Frequency in Hz	60
Total rated load in kW	1.00
Length of supply lead in ft. (m)	6 (2.0)
Type of coolant	R134a
Refrigerant quantity in lbs (kg)	1.03 (0.47)
Standard accessories	
Fragrance flacon	•
Voucher for a second fragrance flacon	•