

WXR960 WCS TDos&IntenseWash

W1 front-loading washing machine:

8 kg | 1600 rpm | Auto Dosing | IntenseWash | Pre-Ironing | SingleWash



- Tested for 20 years of perfect laundry care*
- ENERGY STAR® qualified
- M Touch – simple control by tapping or swiping
- Precise and automatic detergent dispensing with TwinDos®**
- There's no faster way to wash – QuickIntenseWash

* During the development phase of the W1/W2 washing machine series, Miele tested models and core components in 5,000 wash loads (= 5 wash loads per week for 50 weeks per year) in various programs. More: miele.com/20years

** Patent EP 2 784 205

EAN: 4002516937944 / Material number: 12864100 /
Old Material Number: 11XR9605NAM

General information	
Model number	WXR960 WCS TDos&IntenseWash
Manufacturer material number	12864100
EAN number	4002516937944
Marketing class	Diamond
Design	
Stackable	•
Door hinging	left
Side-by-side	•
Slot-in	•
Type	
Product brand	W1 White Edition
Front loaders	•
Spinning	
Max. spin speed	1600
Rinse hold	•
Without spin" function	•
Design	
Appliance color	Lotus white
Control panel color	Lotus white
Door design	Obsidian Black with Chrome ring
Fascia panel version	5° inclined
Control type	Touch control
Control panel	M Touch
Cleaning performance	
Innovative IntenseWash technology	•
TwinDos automatic dispensing of detergent	•
CapDosing portioned dispensing	•
Proven virus hygiene	•
Gentle laundry care	
Honeycomb drum	•
Load in lbs. (kg)	18 (8)
User convenience	
Networking with Miele@home	•
Delay start up to 24 hours	•
Countdown indicator	•
Time display	•
Programme sequence indicator	•
Washing assistant	•
Information text	•
Favorite programs	•
Drum lighting	LED
MultiLingua	•
AutoClean dispenser drawer	•
AddLoad	•

WXR960 WCS TDos&IntenseWash

W1 front-loading washing machine:

8 kg | 1600 rpm | Auto Dosing | IntenseWash | Pre-Ironing | SingleWash



EAN: 4002516937944 / Material number: 12864100 /
Old Material Number: 11XR9605NAM

Smart Extras

Washing Assistant	•
Consumption Dashboard	•
Push notifications	•
MobileStart	•
Smart Home Integration	•
Alexa voice control	•
Google voice control	•
Fill levels	•
AI Diagnostics	•
RemoteUpdate	•

Efficiency

Hot water connection	•
Consumption estimate	•
Low-temperature washing "Cold" and "68°F"	•
Automatic load control	•
Flow meter	•
Foam control	•
DuraLife motor	•

Wash programs

Delicates	•
Silk (hand-washable)	•
Express	•
Dark garments	•
Denim	•
Outdoor	•
Proofing	•
Sportswear	•
Trainers	•
Pillows	•
Down	•
Starch	•
Drain / Spin	•
Normal	•
Wrinkle-free	•
Sanitize	•
Handwash	•
Dress shirts	•
Extra White	•
QuickIntenseWash	•
Woolens	•
QuickRinse	•
Baby Clothes	•
Towels	•
Curtains	•

Washing extras

SingleWash	•
Soak	•

WXR960 WCS TDos&IntenseWash

W1 front-loading washing machine:

8 kg | 1600 rpm | Auto Dosing | IntenseWash | Pre-Ironing | SingleWash



EAN: 4002516937944 / Material number: 12864100 /
Old Material Number: 11XR9605NAM

Pre-rinse	•
SoftSteam with steam	•
Acoustic signal	•
AllergoWash	•
Safety	
Water protection system	Watercontrol-System
Child lock	•
Lock code	•
Optical interface	•
Technical data	
Dimensions (H x W x D) in inches (mm)	33 1/2 (850) x 23 1/2 (596) x 25 3/8 (643)
Dimensions (width) in in. (mm)	23 1/2 (596)
Dimensions (height) in in. (mm)	33 1/2 (850)
Dimensions (depth) in in. (mm)	25 3/8 (643)
Depth with door open in in. (mm)	42 1/2 (1077)
Weight in lbs. (kg)	212 (96)
Voltage in V	120
Fuse rating in A	15
Frequency in Hz	60
Total rated load in kW	1.30
Water intake hose length in ft. (m)	5 (1.60)
Water drain hose length in ft. (m)	4 (1.50)
Length of supply lead in ft. (m)	6 (2)
Standard accessories	
3 capsules	•
UltraPhase 1+2	•
Voucher for 5 x UltraPhases	•