

Triflex HX3 Hardfloor

Cordless stick vacuum cleaner

high suction power | up to 70 min running time | flooring detection | HEPA | hard floor roller



- Dust pickup >99.99%* for thorough and hygienic deep cleaning
- Boost mode: for faster cleaning of heavily soiled areas
- Running time: up to 70 minutes^{***} with VARTA lithium-ion rechargeable battery.
- Patented^{***} 3-in-1 design incl. free-standing function for parking
- HEPA filter: 99.999%**** exhaust air filtration for the purest ambient air
- FloorDetect: flooring detection and power adjustment
- BrilliantLight: particularly bright LED front light for maximum dust detection
- Display: shows time left and important data for stress-free vacuuming
- Twist2open: for hygienic and easy emptying of the dust container
- Carefully developed and manufactured in Germany by Miele & Cie. KG
- Hardfloor Care Tool: soft roller for gentle hard floor cleaning

* When picking up dust on hard floors with cracks, we achieve > 100% dust pickup on power level HI, measured according to IEC 62885-4:2024

** Valid for power level MIN without connected Multi Floor XXL electrobrush

*** Patent: DE 10 2016 105 475 B4

**** 99.999% according to IEC 62885-4:2020/HEPA according to EN 1822-1:2019

EAN: 4002516922568 / Material number: 12878480 /

Old Material Number: 41WDL033USA

General information	
Model number	Triflex HX3 Hardfloor
Manufacturer material number	12878480
EAN number	4002516922568
Design	
Cordless stick vacuum cleaner	•
Product line	Triflex HX3
Motor type	Digital Efficiency Motor
Product type	SWDLO
Appliance type and design	
Appliance color	Casa grey
Cleaning	
Vortex Technology	•
User convenience	
Electronic suction power setting	Display / 3 levels
Boost mode	•
Park system for vacuuming breaks	•
Exchangeable Li-Ion battery	•
3-in-1 design	•
Filter system	
ComfortClean	•
Exhaust filter	HEPA lifetime filter
Dustbag volume in cu. ft. (l)	0.02 (0.5)
Technical data	
Battery type	Li-ion
Nominal battery capacity in mAh	2500
Volume in dB	74.0
Width in inches (mm)	10 1/4 (260)
Height in inch (mm)	51 1/8 (1297)
Depth in inches (mm)	11 (280)
Weight in lbs (kg)	8 (3.6)
Volt	25,2
LOW level running time PowerUnit solo	70
LOW level running time with electrical accessories	38
HIGH level running time with electrical accessories	15
Cleaning area in m ²	160
Recharging time in min.	240
Standard accessories	
HX-DB dust brush	•
XL HX-UN upholstery nozzle	•
HX-CN crevice nozzle	•
HX-AH accessories holder	•
Cleaning brush	No
Wall Mount	•
Power supply unit	•
Hardfloor Care Tool	•