

## Triflex HX3 Plus

Cordless stick vacuum cleaner

high suction power | up to 140 min running time | flooring detection | HEPA



- Dust pickup >99.99%\* for thorough and hygienic deep cleaning
- Boost mode: for faster cleaning of heavily soiled areas
- Running time: up to 140 minutes<sup>\*\*\*</sup> with VARTA lithium-ion rechargeable battery.
- Patented<sup>\*\*\*</sup> 3-in-1 design incl. free-standing function for parking
- HEPA filter: 99.999%\*\*\*\* exhaust air filtration for the purest ambient air
- FloorDetect: flooring detection and power adjustment
- BrilliantLight: particularly bright LED front light for maximum dust detection
- Display: shows time left and important data for stress-free vacuuming
- Twist2open: for hygienic and easy emptying of the dust container
- Carefully developed and manufactured in Germany by Miele & Cie. KG
- Premium set: including Hardfloor Care Tool and second battery

\* When picking up dust on hard floors with cracks, we achieve > 100% dust pickup on power level HI, measured according to IEC 62885-4:2024

\*\* Valid for power level MIN without connected Multi Floor XXL electrobrush and when using 2 rechargeable batteries

\*\*\* Patent: DE 10 2016 105 475 B4

\*\*\*\* 99.999% according to IEC 62885-4:2020/HEPA according to EN 1822-1:2019

EAN: 4002516922575 / Material number: 12878490 /  
Old Material Number: 41WDL034USA

| General information                                 |                          |
|-----------------------------------------------------|--------------------------|
| Model number                                        | Triflex HX3 Plus         |
| Manufacturer material number                        | 12878490                 |
| EAN number                                          | 4002516922575            |
| Design                                              |                          |
| Cordless stick vacuum cleaner                       | •                        |
| Product line                                        | Triflex HX3              |
| Motor type                                          | Digital Efficiency Motor |
| Product type                                        | SWDLO                    |
| Appliance type and design                           |                          |
| Appliance color                                     | Titanium PF              |
| Cleaning                                            |                          |
| Vortex Technology                                   | •                        |
| User convenience                                    |                          |
| Electronic suction power setting                    | Display / 3 levels       |
| Boost mode                                          | •                        |
| Park system for vacuuming breaks                    | •                        |
| Exchangeable Li-Ion battery                         | •                        |
| 3-in-1 design                                       | •                        |
| Filter system                                       |                          |
| ComfortClean                                        | •                        |
| Exhaust filter                                      | HEPA lifetime filter     |
| Dustbag volume in cu. ft. (l)                       | 0.02 (0.5)               |
| Technical data                                      |                          |
| Battery type                                        | Li-ion                   |
| Nominal battery capacity in mAh                     | 2500                     |
| Volume in dB                                        | 74.0                     |
| Width in inches (mm)                                | 10 1/4 (260)             |
| Height in inch (mm)                                 | 51 1/8 (1297)            |
| Depth in inches (mm)                                | 11 (280)                 |
| Weight in lbs (kg)                                  | 8 (3.6)                  |
| Volt                                                | 25,2                     |
| LOW level running time PowerUnit solo               | 2 x 70                   |
| LOW level running time with electrical accessories  | 2 x 38                   |
| HIGH level running time with electrical accessories | 2 x 15                   |
| Cleaning area in m <sup>2</sup>                     | 2 x 160                  |
| Recharging time in min.                             | 240                      |
| Standard accessories                                |                          |
| HX-DB dust brush                                    | •                        |
| XL HX-UN upholstery nozzle                          | •                        |
| HX-CN crevice nozzle                                | •                        |
| HX-AH accessories holder                            | •                        |
| Cleaning brush                                      | No                       |
| Wall Mount                                          | •                        |
| Power supply unit                                   | •                        |
| Additional battery                                  | •                        |
| Hardfloor Care Tool                                 | •                        |