

Triflex HX3 Plus Aqua

Cordless stick vacuum cleaner

high suction power | up to 140 min running time | flooring detection | HEPA | AquaTwister



- AquaTwister: deep cleaning and 360° light for visible cleanliness
- Dust pickup >99.99%* for thorough and hygienic deep cleaning
- Boost mode: for faster cleaning of heavily soiled areas
- Running time: up to 140 minutes*** with VARTA lithium-ion rechargeable battery.
- Patented*** 3-in-1 design incl. free-standing function for parking
- HEPA filter: 99.999%**** exhaust air filtration for the purest ambient air
- FloorDetect: flooring detection and power adjustment
- BrilliantLight: particularly bright LED front light for maximum dust detection
- Display: shows time left and important data for stress-free vacuuming
- Twist2open: for hygienic and easy emptying of the dust container
- Carefully developed and manufactured in Germany by Miele & Cie. KG
- Premium set: including Hardfloor Care Tool and second battery

* When picking up dust on hard floors with cracks, we achieve > 100% dust pickup on power level HI, measured according to IEC 62885-4:2024

** Valid for power level MIN without connected Multi Floor XXL electrobrush and when using 2 rechargeable batteries

*** Patent: DE 10 2016 105 475 B4

**** 99.999% according to IEC 62885-4:2020/HEPA according to EN 1822-1:2019

EAN: 4002516922599 / Material number: 12878520 /
Old Material Number: 41WDL036USA

General information	
Model number	Triflex HX3 Plus Aqua
Manufacturer material number	12878520
EAN number	4002516922599
Design	
Cordless stick vacuum cleaner	•
Product line	Triflex HX3
Motor type	Digital Efficiency Motor
Product type	SWDLO
Appliance type and design	
Appliance color	Obsidian Black
Cleaning	
Vortex Technology	•
User convenience	
Electronic suction power setting	Display / 3 levels
Boost mode	•
Park system for vacuuming breaks	•
Exchangeable Li-Ion battery	•
3-in-1 design	•
Filter system	
ComfortClean	•
Exhaust filter	HEPA lifetime filter
Dustbag volume in cu. ft. (l)	0.02 (0.5)
Technical data	
Battery type	Li-ion
Nominal battery capacity in mAh	2500
Volume in dB	74.0
Width in inches (mm)	10 1/4 (260)
Height in inch (mm)	51 1/8 (1297)
Depth in inches (mm)	11 (280)
Weight in lbs (kg)	8 (3.6)
Volt	25,2
LOW level running time PowerUnit solo	2 x 70
LOW level running time with electrical accessories	2 x 38
HIGH level running time with electrical accessories	2 x 15
Cleaning area in m ²	2 x 160
Recharging time in min.	240
Standard accessories	
HX-DB dust brush	•
XL HX-UN upholstery nozzle	•
HX-CN crevice nozzle	•
HX-AH accessories holder	•
Cleaning brush	No
Wall Mount	•
Power supply unit	•
Additional battery	•
Hardfloor Care Tool	•
AquaTwister	•

Cordless stick vacuum cleaner

high suction power | up to 140 min running time | flooring detection | HEPA | AquaTwister



EAN: 4002516922599 / Material number: 12878520 /

Old Material Number: 41WDL036USA

Voucher for multi-purpose cleaning agent 16.9 fl oz
(500 mL)

UniversalPad

Universal cleaning agent (ml)

Storage tray

•

2

500

•