

KFMC 3632 L

MasterCool™ fridge-freezer

MasterFresh Pro | AirClean system | IceMaker | M Touch Pro | ColdSteel



- Food stays fresh for up to 5 times longer – MasterFresh Pro
- -
- Fresh supplies without unpleasant odors – Longlife AirClean System
- Convenient operation at your fingertips – M Touch Pro
- Sophisticated interior design – ColdSteel

EAN: 4002516962656 / Material number: 12957350 /
Old Material Number: 38363211USA

General information	
Model number	KFMC 3632 L
Manufacturer material number	12957350
EAN number	4002516962656
Marketing class	Platinum
Appliance category	
Fridge-freezer	•
Design	
Built-in	•
Built-in integrated	•
Door hinge side	Left
Convertible hinging	•
Can be installed side-by-side	•
Design	
Design option	Stainless steel front flush-fit installation
Lighting	BrilliantLight
SmartLight	•
User convenience	
Networking with Miele@home	•
Electronic temperature display and control	M Touch Pro
Sabbath mode	•
Freshness system	MasterFresh Pro + DailyFresh ExtraCool
Longlife AirClean System	•
DynaCool	•
Holiday mode	•
NoFrost	•
DuplexCool Pro	•
SoftClose door closing damper	•
SelfClose	•
Number of IceMakers with plumbed water connection	1
IceMaker with mains water connection	•
FullAccess	•
EasyClean	•
MaxLoad hinge	•
Control	
Precise adjustment	Fridge and freezer temperature
Fridge compartment can be switched off	No
Independent temperature control of fridge and freezer compartments	Yes
SuperCool&AirClean	•
SuperFrost	•
No. of temperature zones	3
Eco mode	•
QuickIce	•
Fridge/fridge zone	
Height-adjustable, full-width tempered glass shelves	2

KFMC 3632 L

MasterCool™ fridge-freezer

MasterFresh Pro | AirClean system | IceMaker | M Touch Pro | ColdSteel



EAN: 4002516962656 / Material number: 12957350 /

Old Material Number: 38363211USA

Number of VeggieBoxes	1
No. of PerfectFresh drawers	1
Door rack for tins	2
Inner door racks for bottles	1
Freezer/freezer zone	
Number of freezer baskets	3
of which on telescopic rails	2
Efficiency and sustainability	
Energy Star Qualified	•
Safety	
Spill-proof glass shelves	•
Acoustic door alarm	•
Acoustic temperature alarm, freezer section	•
Technical data	
Niche width in inches (mm), min.	30 (762)
Niche width in inches (mm), max.	30 (762)
Niche height in inches (mm), min.	84 1/8 (2134)
Niche height in inches (mm), max.	84 1/8 (2134)
Niche depth in in.(mm)	25 (635)
Appliance width in in.(mm)	29 7/8 (756)
Appliance height in in.(mm)	83 5/8 (2123)
Appliance depth in in.(mm)	24 (608)
Weight in lbs.(kg)	492 (223.0)
Type of mounting	Fixed door
Maximum fridge compartment door front weight in lbs. (kg)	133 (60)
Maximum freezer compartment door front weight in lbs. (kg)	38 (17)
Fridge compartment volume in cu. ft. (l)	10.91 (309)
4-star freezer compartment volume in cu. ft. (l)	5.62 (159)
Total usable capacity in cu. ft. (l)	16.53 (468)
Current consumption in milliampere (mA)	4000
Voltage in V	110-120
Fuse rating in A	10
Number of phases	1
Frequency in Hz	60
Wire length in ft (m)	9 (3.0)
Replacing bulbs	Customer Service
Standard accessories	
Water filter	Ja
Ice scoop	•