

E 362

Blind stopper

For the sealing of fittings to load carriers.



- Thread M 8 x 1

EAN: 4002511117136 / Material number: 03809630 / Old Material Number: 69736201D

<b>Product category</b>	
Washer-disinfectors, laboratory	•
Large-capacity washer-disinfectors, laboratory	•
Washer-disinfectors, medical	•
Large-capacity washer-disinfectors, medical	•
<b>Machine affiliation</b>	
G 7823	•
G 7824	•
G 7825	•
G 7826	•
PG 8527	•
PG 8528	•
PG 8535	•
PG 8536	•
PG 8562	•
PG 8582	•
PG 8582 CD	•
PG 8504	•
PG 8583	•
PG 8583 CD	•
PG 8592	•
PG 8593	•
<b>Product category</b>	
Other accessories	•
<b>Product properties</b>	
Material	Stainless steel
Colour	Stainless Steel
<b>Area of application</b>	
Reprocessing of laboratory glassware	•
Reprocessing of MIS instruments	•
Reprocessing of ophthalmology instruments	•
Reprocessing of robotic instruments	•
Reprocessing of surgical instruments	•
Reprocessing of lumened instruments	•
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0,00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	14
External dimensions, net width in mm	10
External dimensions, net depth in mm	10
External dimensions, gross height in mm	120
External dimensions, gross width in mm	120
External dimensions, gross depth in mm	170
Diameter in mm	10
Net weight in kg	0,00
Gross weight in kg	0,01