

E 380
Mobile unit
for the optimum loading of narrow necked glassware.



- equipped with 32 nozzles and locking mechanisms
- Equipped with connection for hot air drying
- Bracket for ML/2 for automatic mobile unit recognition

EAN: 4002511116467 / Material number: 03809880 / Old Material Number: 69538001D

Product category	
Washer-disinfectors, laboratory	•
Machine affiliation	
PG 8535	•
PG 8536	•
Product category	
Mobile unit with connection for hot-air drying	•
Mobile unit for narrow-necked glassware	•
Product properties	
Material	Stainless steel, Plastic
Colour	Stainless Steel, Black
Area of application	
Reprocessing of laboratory glassware	•
Capacity	
Narrow-necked glassware [number]	32
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0,00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in mm	502
External dimensions, net width in mm	535
External dimensions, net depth in mm	517
External dimensions, gross height in mm	545
External dimensions, gross width in mm	160
External dimensions, gross depth in mm	530
Net weight in kg	7,90
Gross weight in kg	8,60
Companion pack	
E 351 injector nozzle, Ø 4 mm, length 160 mm [number]	14
E 352 injector nozzle, Ø 6 mm, length 220 mm [number]	18
E 353 clip for injector nozzle E 351 [number]	14
E 354 clip for injector nozzle E 352 [number]	18
Rinse nozzle for powder dispenser [number]	1