

E 460
 Insert
 for the optimum loading of different MIS instruments.



- Suitable for rigid fibre optics of different lengths
- Mesh width on the base 8 x 1 mm sides/lid 7 x 7 x 3 mm
- equipped with 3 brackets for 2 rigid fibre optics

EAN: 4002512183383 / Material number: 04861390 / Old Material Number: 69546001D

Product classification	
Washer-disinfectors, medical	•
Large-capacity washer-disinfectors, medical	•
Machine affiliation	
G 7823	•
G 7824	•
G 7825	•
G 7826	•
PG 8527	•
PG 8528	•
PG 8535	•
PG 8536	•
PG 8562	•
PG 8592	•
Product category	
Insert/module for MIS instruments	•
Other inserts	•
Product properties	
Material	Stainless steel
Colour	Stainless Steel
Area of application	
Reprocessing of MIS instruments	•
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0,00
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in mm	53
External dimensions, net width in mm	100
External dimensions, net depth in mm	430
External dimensions, gross height in mm	95
External dimensions, gross width in mm	170
External dimensions, gross depth in mm	550
Net weight in kg	0,71
Gross weight in kg	0,94