

## PW 6080 Vario [EL LP]

Washing machine, electrically heated

with suspended drum unit, shortest programme running time of 53 min and drain pump.



- Drum volume 80 l, load size 8.0 kg
- Large programme variety – application-specific wash programmes
- Gentle laundry care thanks to the Miele honeycomb drum
- Particularly efficient – low water and energy consumption
- Perfect spinning results – residual moisture 44 %, g-factor 520

\* Residual moisture specification relates to a hot rinse during the last rinse cycle.

EAN: 4002514257174 / Material number: 06942690 / Old Material Number: 51608005D

| Construction type and version  |                     |
|--|---------------------|
| Construction type  | Front loader        |
| Range  | Octoplus            |
| Front  | Octo blue           |
| Load ratio   | 1:10                |
| Load in kg   | 8,0                 |
| Drum volume in l   | 80                  |
| Door opening [Ø] in mm   | 370                 |
| Door opening angle in degrees  | 180                 |
| Door hinge   | right               |
| Maintenance-free motor with frequency converter                        | •                   |
| Stainless steel honeycomb drum   | •                   |
| Application  |                     |
| Suitable for the hotel and catering industry                           | •                   |
| Suitable for retirement and care homes                                 | •                   |
| Suitable for laundrettes   | •                   |
| Suitable for residential homes and apartments                          | •                   |
| Suitable for dry cleaners  | •                   |
| Suitable for commercial laundries                                      | •                   |
| Suitable for small businesses  | •                   |
| Suitable for fire brigades and rescue services                         | •                   |
| Suitable for universities, nurseries, and schools                      | •                   |
| Suitable for hospitals   | •                   |
| Suitable for camp sites  | •                   |
| Suitable for sports clubs  | •                   |
| Suitable for beauty salons, spas, and fitness centres                  | •                   |
| Suitable for domestic use  | •                   |
| Suitable for doctors' and dentists' practices                          | •                   |
| Performance data   |                     |
| Specific water consumption for hot water connection in l/kg            | 8,25                |
| Specific energy consumption for hot water connection in kWh/kg         | 0,06                |
| Programme duration in minutes with cold water connection               | 57                  |
| Programme duration in minutes with cold water and hot water connection | 53                  |
| Residual moisture with cold rinse in %                                 | 49                  |
| Residual moisture with hot rinse in %                                  | 44                  |
| Spin speed in rpm  | 1300                |
| g factor   | 520                 |
| Tested operating hours   | 30000               |
| Control system   |                     |
| Control system   | Profitronic L Vario |
| Programmability  | programmable        |
| Max. delay start in h  | 24                  |
| Time left display  | •                   |
| Programme sequence indicator   | •                   |
| Selectable display languages   | •                   |
| Standard/target grp programmes   |                     |
| Basic programmes   | •                   |
| Programmes for the hotel and catering industry                         | •                   |

## PW 6080 Vario [EL LP]

Washing machine, electrically heated

with suspended drum unit, shortest programme running time of 53 min and drain pump.



EAN: 4002514257174 / Material number: 06942690 / Old Material Number: 51608005D

|   |                                |
|---|--------------------------------|
| Programmes for retirement and care homes                          | •                              |
| Programmes for launderettes                                       | •                              |
| Programmes for residential homes and apartments                   | •                              |
| Programmes for dry cleaners                                       | •                              |
| Programmes for commercial laundries                               | •                              |
| Programmes for small businesses                                   | •                              |
| Programmes for fire brigades and rescue services                  | •                              |
| Programmes for universities, nurseries, and school                | •                              |
| Programmes for hospitals  | •                              |
| Programmes for fast food restaurants                              | •                              |
| Programmes for camp sites   | •                              |
| Programmes for sports clubs                                       | •                              |
| Programmes for beauty clinics, spas, and fitness studios          | •                              |
| Programmes for domestic use                                       | •                              |
| Programmes for doctors' and dentists' practices                   | •                              |
| <b>Dispensing</b>   |                                |
| Detergent drawer  | 3 compartments                 |
| Patented liquid dispensing adapter                                | •                              |
| Maximum number of connections for liquid dispenser pumps [number] | 6                              |
| Empty sensor  | •                              |
| <b>Standard electrical connection</b>                             |                                |
| Heating type  | Electric                       |
| Electrical connection   | 3N AC 400V 50HZ                |
| Heater rating in kW   | 7,95                           |
| Total connected load in kW  | 8,20                           |
| Fuse rating in A  | 16                             |
| <b>Water connection/drainage</b>                                  |                                |
| Cold water [number]   | 1x 1/2" hose w/ 3/4" th. union |
| Hot water [number]  | 1x 1/2" hose w/ 3/4" th. union |
| Grey water (optional) [number]                                    | 1 x 1/2" w/ 3/4" union         |
| Drain pump  | DN 22                          |
| <b>Dimensions and weight</b>                                      |                                |
| External dimensions, height in mm                                 | 1020                           |
| External dimensions, width in mm                                  | 700                            |
| External dimensions, depth in mm                                  | 727                            |
| External dimensions, gross height in mm                           | 1215                           |
| External dimensions, gross width in mm                            | 760                            |
| External dimensions, gross depth in mm                            | 820                            |
| Net weight in kg  | 140,0                          |
| Gross weight in kg  | 148                            |
| Maximum floor load in N   | 2600                           |
| <b>Emissions data</b>   |                                |
| Emission sound pressure level in the workplace                    | <70 dB(A) re 20 µPa            |
| Heat dissipation into the room in MJ/h                            | 3,00                           |
| <b>Features</b>   |                                |
| Imbalance monitoring  | •                              |
| Disinfection rinse  | •                              |
| Temperature monitoring  | •                              |

## PW 6080 Vario [EL LP]

Washing machine, electrically heated

with suspended drum unit, shortest programme running time of 53 min and drain pump.



EAN: 4002514257174 / Material number: 06942690 / Old Material Number: 51608005D

|  |     |
|--|-----|
| Special heater element                               | •   |
| Automatic load control                               | •   |
| Flow meter   | •   |
| Communication slot                                   | •   |
| Machine-independent accessories                      | •   |
| <b>Efficiency and sustainability</b>                 |     |
| Recycling rate in %                                  | 95  |
| <b>Connection options</b>                            |     |
| Payment system                                       | •   |
| Optical interface for service access                 | •   |
| Serial interface module RS 232 (optional)            | •   |
| Peak-load negotiation / energy management (optional) | •   |
| <b>Capacities</b>                                    |     |
| Respirator masks [number]                            | 4-5 |
| Overalls [number]                                    | 1   |
| Over jackets [number]                                | 1-2 |
| Synthetic duvets [number]                            | 1   |
| Synthetic pillows [number]                           | 1-2 |
| Down duvets [number]                                 | 1   |
| Down pillows [number]                                | 1-2 |
| <b>Standards, test certificates and symbols</b>      |     |
| CE   | •   |
| VDE-EMC  | •   |
| VDE  | •   |
| Splash-proof safety rating IPX4                      | •   |
| WEEE   | •   |
| RCM  | •   |
| Complies with Machinery Directive 2006/42/EC         | •   |