

## PT 7186 Vario [EL]

Vented dryer, electrically heated

with shortest programme running time of 37 min for a high laundry throughput.



- Drum volume 180.00 l, load size 8.0 kg
- Large programme variety – application-specific drying programmes
- Precision drying of all fabrics – PerfectDry
- Unique, gentle fabric care – honeycomb drum
- Easy operation – viewing window and large-surface filter

EAN: 4002514334288 / Material number: 07060610 / Old Material Number: 52718601D

Construction type and version	
Construction type	Front loader
Range	Octoplus
Front	Lotus white
Load in kg	8,0
Load ratio	1:22,5
Drum volume in l	180,00
Drying system	Exhaust air
Door opening [Ø] in mm	440
Door opening angle in degrees	180
Door hinge	left
Stainless steel honeycomb drum	Yes
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for laundrettes	•
Suitable for residential homes and apartments	•
Suitable for dry cleaners	•
Suitable for commercial laundries	•
Suitable for small businesses	•
Suitable for fire brigades and rescue services	•
Suitable for studs, riding schools and stables	•
Suitable for universities, nurseries, and schools	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for doctors' and dentists' practices	•
Performance data	
Maximum evaporation capacity in l/hour	8,10
Programme duration in min.	37
Control system	
Control system	Profitronic L Vario
Programmability	programmable
User interface	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Programme sequence indicator	•
Selectable display languages	•
Standard/target grp programmes	
Basic programmes	•
Programmes for facility management	•
Programmes for dry cleaners	•
Programmes for fire brigades and rescue services	•
Programmes for studs, riding schools, and stables	•
Programmes for domestic use	•
Standard electrical connection	
Heating type	Electric

## PT 7186 Vario [EL]

Vented dryer, electrically heated

with shortest programme running time of 37 min for a high laundry throughput.



EAN: 4002514334288 / Material number: 07060610 / Old Material Number: 52718601D

Electrical connection	3N AC 400V 50HZ
Electric heater rating in kW	7,94
Total connected load in kW	8,50
Fuse rating in A	16
<b>Dimensions and weight of dryer</b>	
External dimensions, height in mm	1020
External dimensions, width in mm	700
External dimensions, depth in mm	763
External dimensions, gross height in mm	1215
External dimensions, gross width in mm	760
External dimensions, gross depth in mm	820
Net weight in kg	77,0
Gross weight in kg	88
Maximum floor load in N/m <sup>2</sup>	1000
<b>Emissions data</b>	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	1,62
<b>Features</b>	
Intelligent drum reversal	•
Axial airflow	•
Large-surface filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Communication slot	•
Drying basket (optional)	•
Machine-independent accessories	•
<b>Connection options</b>	
Payment system	•
Serial interface RS 232 (optional)	•
Optical interface for service access	•
Peak-load negotiation / energy management (optional)	•
<b>Capacities</b>	
Respirator masks [number]	4
Overalls [number]	1
Over jackets [number]	1-2
Synthetic duvets [number]	1
Synthetic pillows [number]	1-2
Down duvets [number]	1
Down pillows [number]	1-2
Cloths, 22 g [number]	182
Cotton mops, 40 cm [number]	42
Cotton mops, 50 cm [number]	36
Microfibre mops, 40 cm [number]	66
Microfibre mops, 50 cm [number]	47
Summer horse blankets [number]	1-2
<b>Standards, test certificates and symbols</b>	
CE	•
VDE	•
VDE-EMC	•
Splash-proof safety rating IPX4	•

PT 7186 Vario [EL]

Vented dryer, electrically heated  
with shortest programme running time of 37 min for a high laundry throughput.



EAN: 4002514334288 / Material number: 07060610 / Old Material Number: 52718601D

WEEE

Complies with Machinery Directive 2006/42/EC

•  
•